

WF4115ZT - Wireless



Značka:
Kód produktu: WF4115ZT

Short Description

1.3 Megapixel Edge sensor
20-220x magnification
Adjustable polarizer
Flexible LED Control (FLC)
Free iOS and Android App

Popis

The Dino-Lite WF4115ZT is a Wireless model that is part of the Universal series. Go from wireless to wired and back in an instant. Work wired via USB or work wireless with the attachable WF-20 Wireless adapter.



USB 2.0



1,3 Megapixels
1280 x 1024



Adjustable
~20x-220x



Polarizer
anti-reflection



Measurement
functionality



Flexible LED
Control FLC



Magnification
lock



Exchangeable
cap



Standard working
distance

The WF4115ZT is equipped with premium features such as Flexible LED control (FLC),

integrated polarizer, extensive measurement functionality.

The main features of the WF4115ZT are:

- Completely wireless solution (including WF20)
- 20-220x magnification
- 1.3 Megapixel Edge sensor
- Extensive measurement functionality
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

Working distance/ field of view/ depth of field:

| MAGNIFICATION RATE | WORKING DISTANCE * * Without front cap | FIELD OF VIEW(X) | FIELD OF VIEW(Y) | DEPTH OF FIELD Unit = mm |
|-----------------------------------|---|------------------|------------------|-----------------------------|
| Listed values may differ slightly | | | | |
| 20 | 60.2 | 19.5 | 14.6 | 2.5 |
| 30 | 33.5 | 13.0 | 9.7 | 1.8 |
| 40 | 20.9 | 9.8 | 7.3 | 1.5 |
| 50 | 13.9 | 7.8 | 5.8 | - |
| 60 | 9.7 | 6.5 | 4.8 | - |
| 70 | 7.1 | 5.6 | 4.2 | 1.0 |
| 80 | 5.5 | 4.9 | 3.6 | - |
| 90 | 4.5 | 4.3 | 3.2 | - |
| 100 | 4.1 | 3.9 | 2.9 | - |
| 110 | 4.0 | 3.6 | 2.7 | - |
| 120 | 4.1 | 3.3 | 2.4 | - |
| 130 | 4.5 | 3.0 | 2.2 | - |
| 140 | 5.0 | 2.8 | 2.1 | - |
| 150 | 5.6 | 2.6 | 1.9 | - |
| 160 | 6.3 | 2.4 | 1.8 | - |
| 170 | 7.1 | 2.3 | 1.7 | - |
| 180 | 8.0 | 2.2 | 1.6 | - |
| 190 | 8.9 | 2.1 | 1.5 | - |
| 200 | 9.9 | 2.0 | 1.5 | - |
| 210 | 10.9 | 1.9 | 1.4 | - |
| 220 | 11.9 | 1.8 | 1.3 | 0.1 |

Specifikace

| Lighting | |
|-----------------------------------|--|
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | Yes (N3C-D included) |
| Emission filter | No |
| Polarizer | Yes, linear |
| Optics | |
| Magnification | 20x ~ 220x |
| Macro zoom | No |
| Working distance | Standard |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 1.3 Megapixel (1280x1024) |
| Maximum frame rate | 30 fps |
| Compatibility | |
| Interface | USB 2.0 |
| Operating system | Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only) |
| Software | DinoCapture 2.0 (Windows) cable + wireless, DinoXcope (Mac OS) cable only, DinoConnect wireless only |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF |
| Supported image formats (MacOS) | JPEG, PNG |
| Supported video formats (MacOS) | MOV |
| Imaging standards | DirectShow, UVC |
| Wifi | Yes |
| Housing | |
| Housing material | Composite/ plastic housing |
| Dimensions | 11.4cm (L) x 3.3cm (D) |
| Weight | 111g |

| | |
|----------------------|---|
| Cable length | 1.8m |
| Features | |
| Special feature | Flexible LED Control (FLC) |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | No |
| Information | |
| Package contents | Microscope, WF-20, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €800,00 - €1000,00 |

Product Gallery