

# N3C-S Sidelight cap

**Zna?ka:** Dino-Lite  
**Kód produktu:** N3C-S



## Short Description

Usage: Working with shiny objects (metal/plastics/PCB.jewelry etc.).

## Popis

The interchangeable front caps are designed to be used with Dino-Lite Edge and Edge<sup>PLUS</sup> series models. The caps provide additional versatility to Dino-Lite digital microscope applications. Use the sidelight cap to light from the side for highlighting the texture and depth of targets at short working distances. When working with shiny objects (metal/plastics/PCB/jewelry,etc)

## Compatibility

All Dino-Lite Edge/Edge<sup>PLUS</sup> models

## N3C caps overview

|    | MODEL   | VERSIO<br>N                                      | N3C-O    | N3C-E                | N3C-C      | N3C-L    | N3C-<br>D/D2    | N3C-S            |
|----|---|--|----------|----------------------|------------|----------|-----------------|------------------|
|    |   |  | Open cap | Extended<br>open cap | Closed cap | Long cap | Diffuser<br>cap | Sidelight<br>cap |
| AM | 4115,<br>4117,<br>4515,<br>4517,<br>4815, 491 | Standard<br>models:<br>ZT, ZTL,<br>MZT,<br>MZTL, | ?        | ?                    | ?          | ?        | ?               | ?                |

|    |   |   |                         |   |   |   |   |   |
|----|---|---|-------------------------|---|---|---|---|---|
|    | 7, 7115,<br>7515,<br>7915,<br>73115,<br>73515,<br>73915 | ZTW   |                         |   |   |   |   |   |
| AM | 4115,<br>4515,<br>4117,<br>4517,<br>7115                | Ultraviolet<br>/Infrared<br>models:<br>FVW,<br>FUW, FIT,<br>FJT, FKT ,<br>FUT,<br>FVT,  | ?<br>(black<br>version) | x | x | x | x | x |
| AM | 4115,<br>4117,<br>4515,<br>4517,<br>4815                | Fluorescen<br>t models:<br>CFVW,<br>DFRW,<br>GFBW,<br>G2FBW,<br>GRFBY,<br>YFGW,<br>RFYW | ?<br>(black<br>version) | x | x | x | x | x |
| AM | 4515,<br>7515,<br>73515                                 | High magn<br>ification<br>models:<br>ZT4, T5,<br>T8,<br>MT4A,<br>MT8A                   | ?                       | x | ? | x | x | x |
| AM | 4115,<br>7115,<br>73115                                 | Extra<br>Long<br>Working<br>distance<br>models:<br>ZT, ZTF                              | ?                       | x | x | x | x | x |
| AM | 5216,<br>5218   | VGA,<br>HDMI<br>models:<br>ZT, ZTL  | ?                       | ? | ? | ? | ? | ? |