

# AF4115ZT

**Marke:**

**Artikelnummer:** AF4115ZT



## Short Description

1.3 Megapixel Edge sensor

20x ~ 220x magnification

Adjustable Polarizer

Flexible LED Control (FLC)

Extensive measurement functionality

## Beschreibung

The Dino-Lite AF4115ZT is part of Universal series and connects to your device via USB. The AF4115ZT is Wireless-ready, but requires the (optional) [WF-20](#) to make it a fully wireless solution.



USB 2.0



1,3 Megapixels  
1280 x 1024



Adjustable  
~20x-220x



Polarizer  
anti-reflection



Measurement  
functionality




Flexible LED  
Control FLC



Magnification  
lock



Standard working  
distance



Exchangeable  
cap

The AF4115ZT is equipped with premium features such as Flexible LED control (FLC),

integrated polarizer, extensive measurement functionality.

**The main features of the AF4115ZT are:**

- Wireless-ready, requires the WF-20 adapter (optional)
- 20x ~ 220x magnification
- 1.3 Megapixel Edge sensor
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

**Working distance/field of view/depth of field**

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE *</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
<b>20</b>	60.2	19.5	15.6	2.5
<b>30</b>	33.5	13	10.4	1.8
<b>40</b>	20.9	9.8	7.8	1.5
<b>50</b>	13.9	7.8	6.3	
<b>60</b>	9.7	6.5	5.2	
<b>70</b>	7.1	5.6	4.5	1.0
<b>80</b>	5.5	4.9	3.9	
<b>90</b>	4.5	4.3	3.5	
<b>100</b>	4.1	3.9	3.1	
<b>110</b>	4	3.6	2.8	
<b>120</b>	4.1	3.3	2.6	
<b>130</b>	4.5	3	2.4	
<b>140</b>	5	2.8	2.2	
<b>150</b>	5.6	2.6	2.1	
<b>160</b>	6.3	2.4	2	
<b>170</b>	7.1	2.3	1.8	
<b>180</b>	8	2.2	1.7	
<b>190</b>	8.9	2.1	1.6	
<b>200</b>	9.9	2	1.6	
<b>210</b>	10.9	1.9	1.5	
<b>220</b>	11.9	1.8	1.4	0.1

Listed values may differ slightly  
\* Without front cap

Unit = mm

## Spezifikation

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.12 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
Housing	
Housing material	Composite/ plastic housing
Dimensions	11.4cm (L) x 3.3cm (D)
Weight	111g
Cable length	1.8m
Features	
Special feature	Flexible LED Control (FLC)

Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, Carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€500,00 - €600,00

### **Product Gallery**