

AM4013MTL



Marke:
Artikelnummer: AM4013MTL

Short Description

1.3 Megapixel resolution
Robust metal housing
10x ~ 90x magnification
Long working distance

Beschreibung

Dino-Lite professional model in aluminium alloy housing and long working distance and Microtouch. The aluminium housing offers enhanced protection and durability and has the best look and feel.



USB 2.0



Measurement
functionality



Continuous
~10-90x



1,3 Megapixels
1280 x 1024



8 White LEDs
switchable



Metal
housing



Long working
distance

Working distance/field of view/depth of field

| MAGNIFICATION RATE | WORKING DISTANCE | FIELD OF VIEW(X) | FIELD OF VIEW(Y) | DEPTH OF FIELD |
|---------------------------|-------------------------|-------------------------|-------------------------|-----------------------|
| 20 | 151.0 | 19.6 | 15.6 | 6 |
| 30 | 101.0 | 13.0 | 10.4 | 3.4 |
| 40 | 77.2 | 9.8 | 7.8 | 2.2 |
| 50 | 64.1 | 7.8 | 6.3 | 1.65 |
| 60 | 56.2 | 6.5 | 5.2 | . |
| 70 | 51.3 | 5.6 | 4.5 | . |
| 80 | 48.3 | 4.9 | 3.9 | . |
| 90 | 46.6 | 4.3 | 3.5 | 0.8 |

Listed values may differ slightly

Unit = mm

Spezifikation

| | |
|-----------------------------------|---|
| Lighting | |
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | No |
| Emission filter | No |
| Polarizer | No |
| Optics | |
| Magnification | 10x ~ 90x |
| Macro zoom | No |
| Working distance | Long |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 1.3 Megapixel (1280x1024) |
| Maximum frame rate | 30 fps |
| Compatibility | |
| Interface | USB 2.0 |
| Operating system | Windows 7,8,10 & 11, MacOS 10.9 and up |
| Software | DinoCapture 2.0 (Windows), DinoXcope (Mac OS) |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF |
| Supported image formats | JPEG, PNG |

| | |
|-------------------------|---|
| (MacOS) | |
| Supported video formats | MOV |
| (MacOS) | |
| Imaging standards | DirectShow, UVC |
| Wifi | Wireless-ready, requires the WF-10 WiFi streamer (optional) |
| Housing | |
| Housing material | Metal housing |
| Dimensions | 10.5cm (L) x 3.2cm (D) |
| Weight | 140g |
| Cable length | 1.8m |
| Features | |
| Special feature | No |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | Yes |
| Information | |
| Package contents | Microscope, carry pouch, software CD, calibration target, user manual |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €350,00 - €550,00 |

Product Gallery