

AM4113ZTL



Marke:

Artikelnummer: AM4113ZTL

Short Description

1.3 Megapixel resolution

With magnification lock

10x ~ 90x Magnification and Long working distance

Polarizer (anti-reflection)

Beschreibung

By using a special polarization filter, the AM4113ZTL is the right choice when working with high glare materials such as plastics and metals. This model also has a long working distance.



USB 2.0



Measurement
functionality



CONTINUOUS
~20x-90x



1,3 Megapixels
1280 x 1024



8 White LEDs
switchable



Magnification
lock



Long working
distance



Polarizer
anti-reflection

Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	151.0	19.6	15.6	
30	101.0	13.0	10.4	3.4
40	77.2	9.8	7.8	2.2
50	64.1	7.8	6.3	1.65
60	56.2	6.5	5.2	.
70	51.3	5.6	4.5	.
80	48.3	4.9	3.9	.
90	46.6	4.3	3.5	0.8
Listed values may differ slightly				Unit = mm

6

Spezifikation

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 90x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats	JPEG, PNG

(MacOS)	
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Housing	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	105g
Cable length	1.8m
Features	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, ZT-Z-CC1 cap closure, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€400,00 - €600,00