

AM4517MZT



Marke:

Artikelnummer: AM4517MZT EDGE PLUS

Short Description

1.3 Megapixel

10-220x magnification

Polarizer

Flexible LED Control (FLC)

Automatic Magnification Reading (AMR)

Robust metal housing

Beschreibung


The Dino-Lite AM4517MZT is part of the EDGE ^{PLUS} series, a special category within the Universal range. It offers a magnification range of 10-220x with 1.3MP and a USB 2.0 connection at 30fps. It offers superb image quality and clarity and color reproduction in a robust, compact and appealing metal housing.



ADJUSTABLE
~10-220x



USB 2.0



Exchangeable
cap




Polarizer
anti-reflection



Metal
housing



Flexible LED
Control FLC



The AMR function automatically detects and displays the magnification of the Dino-Lite. The magnification is displayed within the Dino-Lite software and stored with the captured picture and simplifies the measuring process. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the AM4517MZT are:

- 1.3 Megapixel EDGE *PLUS* sensor
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- 10-220x magnification
- Adjustable polarizer
- 30fps
- Metal housing
- And more...

Working distance/field of view/depth of field

| MAGNIFICATION RATE | WORKING DISTANCE* | FIELD OF VIEW(X) | FIELD OF VIEW(Y) | DEPTH OF FIELD |
|---------------------------|--------------------------|-------------------------|-------------------------|-----------------------|
| 20 | 59.5 | 19.5 | 14.7 | 5.36 |
| 30 | 32.9 | 13.0 | 9.8 | 2.58 |
| 40 | 20.2 | 9.8 | 7.3 | 1.56 |
| 50 | 13.2 | 7.8 | 5.9 | 1.07 |
| 60 | 9. | 6.5 | 4.9 | 0.79 |
| 70 | 6.4 | 5.6 | 4.2 | 0.62 |
| 80 | 4.8 | 4.9 | 3.7 | 0.5 |
| 90 | 4 | 4.3 | 3.3 | 0.42 |
| 100 | 3.5 | 3.9 | 2.9 | 0.36 |
| 110 | 3.3 | 3.6 | 2.7 | 0.31 |
| 120 | 3.5 | 3.3 | 2.4 | 0.27 |
| 130 | 3.8 | 3.0 | 2.3 | 0.24 |

| | | | | |
|--|---------------------------|-----|-----|------------------|
| 140 | 4.3 | 2.8 | 2.1 | 0.22 |
| 150 | 4.9 | 2.6 | 2.0 | 0.2 |
| 160 | 5.6 | 2.4 | 1.8 | 0.18 |
| 170 | 6.4 | 2.3 | 1.7 | 0.17 |
| 180 | 7.3 | 2.2 | 1.6 | 0.15 |
| 190 | 8.2 | 2.1 | 1.5 | 0.14 |
| 200 | 9.2 | 2.0 | 1.5 | 0.13 |
| 210 | 10.2 | 1.9 | 1.4 | 0.13 |
| 220 | 11.3 | 1.8 | 1.3 | 0.12 |
| Listed values may differ slightly | *Without front cap | | | Unit = mm |

Spezifikation

| Lighting | |
|-----------------------------------|---|
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | Yes (N3C-D included) |
| Emission filter | No |
| Polarizer | Yes, linear |
| Optics | |
| Magnification | 10x ~ 220x |
| Macro zoom | No |
| Working distance | Standard |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 1.3 Megapixel (1280x960) |
| Maximum frame rate | 30 fps |
| Compatibility | |
| Interface | USB 2.0 |
| Operating system | Windows 7, 8, 10 & 11, MacOS 11.1 and up |
| Software | DinoCapture 2.0 (Windows), DinoXcope (Mac OS) |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF (max 1.3MP) |
| Supported image formats (MacOS) | JPEG, PNG |

| | |
|---------------------------------|--|
| Supported video formats (MacOS) | MOV |
| Imaging standards | DirectShow, UVC |
| Wifi | Wireless-ready, requires the WF-10 WiFi streamer (optional) |
| Housing | |
| Housing material | Metal housing |
| Magnification lock | Yes |
| Dimensions | 10.5cm (L) x 3.3cm (D) |
| Weight | 90g |
| Cable length | 1.5m |
| Features | |
| Special feature | Flexible LED Control (FLC) & Automatic Magnification Reading (AMR) |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | Yes |
| Information | |
| Package contents | Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover box with N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €900,00 - €1100,00 |

Product Gallery

