

# AF4135ZTLE

**Marke:**

**Artikelnummer:** AF4135ZTLE


## Short Description

1.3 Megapixel Edge sensor  
10x~200x magnification  
Flexible LED Control (FLC)  
Polarizer  
Wireless-ready

## Beschreibung

The Dino-Lite AF4135ZTLE is part of Long Working Distance (LWD) series and connects to your device via USB. The AF4135ZTLE is Wireless-ready, but requires the (optional) WF-20 to make it a fully wireless solution.

In comparison, the AF4x35 series provides a similar working distance range but achieves higher magnifications compared to the AM4x15 series.



---

The AF4135ZTLE is equipped with premium features such as Flexible LED Control (FLC), integrated polarizer, extensive measurement functionality.

## The main features of the AF4135ZTLE are:

- Wireless-ready, requires the WF-20 adapter (optional)
- 10x~200x magnification
- 1.3 Megapixel Edge sensor

- Integrated polarizer (anti-reflection)
- Extensive measurement functionality
- Flexible LED Control (FLC)
- And more...

### Working distance/field of view/depth of field

Magnification Rate	Working Distance *	Field of View(x)	Field of View(y)	Depth of Field
Listed values may differ slightly	* Without front cap			Unit = mm
10	355.8	39.1	29.3	55.2
20	173.0	19.5	14.7	14.5
30	113.1	13.0	9.8	6.7
40	83.8	9.8	7.3	3.9
50	66.8	7.8	5.9	2.6
60	55.9	6.5	4.9	1.9
70	48.6	5.6	4.2	1.5
80	43.4	4.9	3.7	1.2
90	39.8	4.3	3.3	1.0
100	37.1	3.9	2.9	0.8
110	35.2	3.6	2.7	0.7
120	33.8	3.3	2.4	0.6
130	32.9	3.0	2.3	0.5
140	32.3	2.8	2.1	0.5
150	32.0	2.6	2.0	0.4
160	31.8	2.4	1.8	0.4
170	31.9	2.3	1.7	0.4
180	32.1	2.2	1.6	0.3
190	32.5	2.1	1.5	0.3
200	33.0	2.0	1.5	0.3

### Spezifikation

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)

Emission filter	No
Polarizer	Yes, linear
<b>Optics</b>	
Magnification	10x ~ 200x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
<b>Sensor</b>	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.12 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
<b>Housing</b>	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	11.4cm (L) x 3.3cm (D)
Weight	111g
Cable length	1.8m
<b>Features</b>	
Special feature	Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C-

	Closed cap, N3C-D- diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€550,00 - €750,00

## **Product Gallery**