

# WF7515MZT

**Marke:**

**Artikelnummer:** Wf7515MZT - EDGE



## Short Description

5 Megapixel resolution  
Robust metal housing  
10-220x magnification  
Polarizer  
Flexible LED Control (FLC)  
Automatic Magnification Reading (AMR)  
Wireless

## Beschreibung

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features such as flexible LED control (FLC), Automatic Magnification Reading (AMR) and full aluminum body, the Dino-Lite WF7515MZT is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite WF7515MZT offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Automatic  
Magnification  
Reading (AMR)



ADJUSTABLE  
~10-220x



The WF7515MZT is part of the universal range and with its standard working distance and wide magnification range from 10 – 220x, it is suitable for a wide range of applications. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc. The AMR function is of particular importance when the measurement functions are frequently used.

**The main features of the WF7515MZT are:**

- 5 Megapixel Edge sensor
- 10-220x magnification
- Integrated polarizer
- Aluminum housing
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- Wireless
- And more...

**Working distance/field of view/depth of field**

MAGNIFICATION RATE	WORKING DISTANCE 1	WORKING DISTANCE 2*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>		<b>* Without front cap</b>			<b>Unit = mm</b>

10	-	142.6	39.6	29.7	2.6
20	52.7	60.1	19.5	15.6	2.5
30	26.0	33.5	13.0	10.4	1.8
40	13.4	20.9	9.8	7.8	1.5
50	6.4	13.9	7.8	6.3	-
60	2.2	9.7	6.5	5.2	-
70	-	7.1	5.6	4.5	1.0
80	-	5.5	4.9	3.9	-
90	-	4.5	4.3	3.5	-
100	-	4.1	3.9	3.1	-
110	-	4.0	3.6	2.8	-
120	-	4.1	3.3	2.6	-
130	-	4.5	3.0	2.4	-
140	-	5.0	2.8	2.2	-
150	-	5.6	2.6	2.1	-
160	-	6.3	2.4	2.0	-
170	-	7.1	2.3	1.8	-
180	-	8.0	2.2	1.7	-
190	-	8.9	2.1	1.6	-
200	-	9.9	2.0	1.6	-
210	-	10.9	1.9	1.5	-
220	-	11.9	1.8	1.4	0.1

## Spezifikation

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	5 Megapixel (2592x1944)
Maximum frame rate	30 fps
Compatibility	

Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only)
Software	DinoCapture 2.0 (Windows) cable + wireless, DinoXscope (Mac OS) cable only, DinoConnect wireless only
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV (max 1.3MP)
Imaging standards	DirectShow, UVC
Wifi	Yes
<b>Housing</b>	
Housing material	Metal housing
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	135gr
Cable length	1.8m
<b>Features</b>	
Special feature	Automatic Magnification Reading (AMR), Flexible LED Control (FLC).
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1400,00 - €1600,00

## Product Gallery

