

# AM73515MZTL



**Brand:**

**Product Code:** AM73515MZTL

## Short Description

5 Megapixel Edge sensor

USB 3.0, maximum 45fps

10-140 magnification

Automatic Magnification Reading (AMR)

Flexible LED Control (FLC)

Long working distance (3~24cm)

Polarizer














## Description

With the use of the USB 3.0 connection the AM73515MZTL is able to capture smooth and high-quality images. The Edge series optics and the special feature Flexible LED Control (FLC) and Automatic Magnification Reading (AMR) makes the AM73515MZTL the best choice for the more demanding applications.

USB 3.0 adds a new transfer mode called "SuperSpeed" (SS) capable of transferring data up to 5Gbits/s (625MB/s). Dino-Lite models with USB 3.0 offer an image transfer speed of up to 45FPS at a 1280 x 960 resolution. SuperSpeed allows you to take advantage of the full power of the Dino-Lite Edge Series optics including improved colour accuracy and image quality. The AMR function automatically detects and displays the magnification of the Dino-Lite. The magnification is displayed within the Dino-Lite software and stored with the captured picture and simplifies the measuring process. The AM73515MZTL is one of the most high-end Dino-Lite products available and the top-

level product within the Dino-Lite USB 3.0 range. For professionals who are looking for high speed data transfer, the best available image quality and are looking for advanced features this is the model of choice.

---

 USB 3.0	 High speed	 Adjustable ~10x - 140x
 Metal housing	 Exchangeable cap	 Magnification lock
 5 megapixel 2592 x 1944	 8 White LEDs switchable	 Measurement functionality
 Polarizer anti-reflection	 Long working distance	 Flexible LED Control FLC
 Automatic Magnification Reading (AMR)		

---

The Dino-Lite AM73515MZTL is a USB 3.0 model with a magnification range of 10x - 140x and a Long Working Distance of up to 24 cm. This model is member of the Dino-Lite Edge family with the latest, cutting-edge optics, an unmatched 5 megapixel sensor and several special features such as:

- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Built-in polarization filter
- Full metal body
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- And more...

### Optical Data Table

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE*</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
<b>10</b>	234.5	39.0	29.2	12.0
<b>20</b>	112.5	19.5	14.6	4.5
<b>30</b>	72.5	13.0	9.7	3.1
<b>40</b>	54.5	9.8	7.3	1.8

<b>50</b>	43.5	7.8	5.8	1.2
<b>60</b>	37.5	6.5	4.8	0.9
<b>70</b>	33.7	5.6	4.2	0.6
<b>80</b>	31.3	4.9	3.6	0.5
<b>90</b>	29.9	4.3	3.2	0.37
<b>100</b>	29.2	3.9	2.9	0.28
<b>110</b>	29.1	3.5	2.6	0.22
<b>120</b>	29.3	3.3	2.4	0.17
<b>130</b>	29.8	3.0	2.2	0.12
<b>140</b>	30.5	2.8	2.1	0.09
<b>Listed values may differ slightly</b>	<b>*Without front cap</b>			<b>Unit = mm</b>

## Specification

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 140x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	5.0 Megapixel (2560x1920)
Maximum frame rate	45fps (max 20fps video recording)
Compatibility	
Interface	USB 3.0, Cable included**
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats	JPEG, PNG

(MacOS)	
Supported video formats (MacOS)	MOV (max 1.3MP)
Imaging standards	DirectShow, UVC
Wifi	No
<b>Housing</b>	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	11.9cm (L) x 3.3cm (H)
Weight	110g
Cable length	1.8m
<b>Features</b>	
Special feature	Automatic Magnification Reading (AMR) Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1100,00 - €1300,00
Note	**Dino-Lite USB 3.0 models use a custom USB-A and USB-C cable that is specifically designed for Dino-Lite

## Product Gallery