

AM4517MZTL



Brand:

Product Code: AM4517MZTL EDGE PLUS

Short Description

1.3 Megapixel

10-140x Magnification

Long working distance

Polarizer

Flexible LED Control (FLC)

Automatic Magnification Reading (AMR)

Robust metal housing

Description

The Dino-Lite AM4517MZTL is part of the EDGE^{PLUS} series, a special category within the Long Working Distance (LWD) range. It offers a magnification range of 10-140x with 1.3MP and a USB 2.0 connection at 30fps. It offers superb image quality, clarity and color reproduction in a robust, compact and appealing metal housing.



1.3 megapixel
1280 x 1024




USB 2.0



Continuous
~10x - 140x



Exchangeable
cap



Polarizer
anti-reflection



Metal
housing



Flexible LED
Control FLC



Measurement
functionality



Automatic
Magnification
Reading (AMR)



Long working
distance



Magnification
lock

The AMR function automatically detects and displays the magnification of the Dino-Lite. The magnification is displayed within the Dino-Lite software and stored with the captured picture and simplifies the measuring process. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the AM4517MZTL are:

- 1.3 Megapixel EDGE^{PLUS} sensor
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- 10-140x magnification
- Long working distance
- Adjustable polarizer
- 30fps
- Metal housing
- And more...

Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	237.6	39.1	29	24.61
20	115.0	19.5	14.7	6.68
30	75.4	13.0	9.8	3.21
40	56.7	9.8	7.3	1.94
50	46.4	7.8	5.9	1.33
60	40.1	6.5	4.9	0.98
70	36.3	5.6	4.2	0.76
80	34.0	4.9	3.7	0.62
90	32.6	4.3	3.3	0.51
100	31.9	3.9	2.9	0.44

110	31.7	3.6	2.7	0.38
120	31.9	3.3	2.4	0.33
130	32.4	3.0	2.3	0.3
140	33.2	2.8	2.1	0.27
Listed values may differ slightly	*Without front cap			Unit = mm

Specification

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 140x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280 x 960)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 11.1 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF (max 1.3MP)
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)

Housing	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.3cm (D)
Weight	130g
Cable length	1.5m
Features	
Special feature	Flexible LED Control (FLC) & Automatic Magnification Reading (AMR)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
Information	
Package contents	Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover box with N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€900,00 - €1100,00

Product Gallery



