

WF7915MZT

Brand:

Product Code: WF7915MZT



Short Description

Wireless

5 Megapixel resolution

Extended Depth of Field (EDOF)

Extended Dynamic Range (EDR)

Flexible LED Control (FLC)

Automatic Magnification Reading (AMR)

10-220x magnification

Description

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features, the Dino-Lite WF7915MZT is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite WF7915MZT offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Adjustable
~10-220x



5 megapixel
2592 x 1944



With the Extended Dynamic Range (EDR) feature, the details of darker or brighter areas within the object can be revealed by stacking images at different exposure levels. The Extended Depth of Field (EDOF) feature automatically stacks images at different focus level to improve the depth of field on rough or uneven surfaces. With the built-in Automatic Magnification Reading (AMR), measurements can be performed easily and quickly. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the WF7915MZT are:

- 5 Megapixel Edge sensor
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- Automatic Magnification Reading (AMR)
- Adjustable polarizer
- Flexible LED Control (FLC)
- 10-220x magnification
- Wireless

*(*EDOF/EDR only functions under Windows OS)*

Working distance/field of view/depth of field

| M | WD | FOV (x) | FOV (y) | DOF |
|----------|-----------|----------------|----------------|------------|
| 10 | 142.6 | 39.6 | 29.7 | 26.0 |
| 20 | 60.1 | 19.8 | 14.8 | 7.0 |
| 30 | 33.6 | 13.2 | 9.9 | 3.3 |
| 40 | 21.0 | 9.9 | 7.4 | 2.0 |
| 50 | 14.0 | 7.9 | 5.9 | 1.4 |

| | | | | |
|-----|------|-----|-----|-----|
| 60 | 9.8 | 6.6 | 4.9 | 1.0 |
| 70 | 7.3 | 5.7 | 4.2 | 0.8 |
| 80 | 5.7 | 4.9 | 3.7 | 0.6 |
| 90 | 4.8 | 4.4 | 3.3 | 0.5 |
| 100 | 4.3 | 4.0 | 3.0 | 0.4 |
| 110 | 4.2 | 3.6 | 2.7 | 0.4 |
| 120 | 4.3 | 3.3 | 2.5 | 0.3 |
| 130 | 4.7 | 3.0 | 2.3 | 0.3 |
| 140 | 5.2 | 2.8 | 2.1 | 0.3 |
| 150 | 5.8 | 2.6 | 2.0 | 0.3 |
| 160 | 6.5 | 2.5 | 1.9 | 0.2 |
| 170 | 7.3 | 2.3 | 1.8 | 0.2 |
| 180 | 8.1 | 2.2 | 1.6 | 0.2 |
| 190 | 9.1 | 2.1 | 1.6 | 0.2 |
| 200 | 10.0 | 2.0 | 1.5 | 0.2 |
| 210 | 11.0 | 1.9 | 1.4 | 0.2 |
| 220 | 12.1 | 1.8 | 1.3 | 0.2 |

Listed values may differ slightly * Without front cap Unit = mm

Specification

| | |
|------------------------|------------------------------------|
| Lighting | |
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | Yes (N3C-D included) |
| Emission filter | No |
| Polarizer | Yes, linear |
| Optics | |
| Magnification | 10x ~ 220x |
| Macro zoom | No |
| Working distance | Standard |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 5 Megapixel (2592x1944) |
| Maximum frame rate | 30 fps |
| Compatibility | |

| | |
|-----------------------------------|--|
| Interface | USB 2.0 |
| Operating system | Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only) |
| Software | DinoCapture 2.0 (Windows) cable + wireless, DinoXscope (Mac OS) cable only, DinoConnect wireless only |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF |
| Supported image formats (MacOS) | PNG, JPEG |
| Supported video formats (MacOS) | MOV (max 1.3MP) |
| Imaging standards | DirectShow, UVC |
| Wifi | Yes |
| Housing | |
| Housing material | Metal housing |
| Magnification lock | Yes |
| Dimensions | 10.5cm (L) x 3.2cm (D) |
| Weight | 137g |
| Cable length | 1.8m |
| Features | |
| Special feature | Automatic Magnification Reading (AMR), Extended Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC). |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | Yes |
| Information | |
| Package contents | Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €1500,00 - €1700,00 |

Product Gallery

