

RK-10F / RK-10FS

Marca:

Código del producto: RK-10F / RK-10FS



Short Description

Quick Release Button

Fine-Focus Knob

Anti-Backlash Lock

Arm Screw

HD-M2A

Descripción

The RK-10F is an upgraded version of the RK-10, featuring an improved quick release button with an anti-backlash mechanism that enhances its ability to make precise focus adjustments, ensuring smoother and more responsive operation.

The RK-10FS incorporates a heavier antistatic baseplate that suppresses external vibrations, making it an optimal choice for stable operation under high-magnification inspections.

Especificación

Housing	
Dimensions	226 mm (H) x 150 mm (D) x 220 mm (L)
Dimensions	226 mm (H) x 150 mm (D) x 220 mm (L)
Weight	Approx. 1050 g
Weight	Approx. 1900 g

Features	
ESD safe	Yes
Information	
Package contents	Stand, HD-P1 holder, RK-10-EX horizontal arm
Warranty information	2 years European warranty
Accessory range:	Professional stands
Price range	€300,00 - €450,00

Product Gallery

