

# AM4517MZT



**Marca:**  
**Código del producto:** AM4517MZT EDGE PLUS

## Short Description

1.3 Megapixel  
10-220x magnification  
Polarizer  
Flexible LED Control (FLC)  
Automatic Magnification Reading (AMR)  
Robust metal housing

## Descripción


The Dino-Lite AM4517MZT is part of the EDGE *PLUS* series, a special category within the Universal range. It offers a magnification range of 10-220x with 1.3MP and a USB 2.0 connection at 30fps. It offers superb image quality and clarity and color reproduction in a robust, compact and appealing metal housing.



ADJUSTABLE  
~10-220x



USB 2.0



Exchangeable  
cap




Polarizer  
anti-reflection



Metal  
housing



Flexible LED  
Control FLC



The AMR function automatically detects and displays the magnification of the Dino-Lite. The magnification is displayed within the Dino-Lite software and stored with the captured picture and simplifies the measuring process. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

**The main features of the AM4517MZT are:**

- 1.3 Megapixel EDGE *PLUS* sensor
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- 10-220x magnification
- Adjustable polarizer
- 30fps
- Metal housing
- And more...

**Working distance/field of view/depth of field**

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE*</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
<b>20</b>	59.5	19.5	14.7	5.36
<b>30</b>	32.9	13.0	9.8	2.58
<b>40</b>	20.2	9.8	7.3	1.56
<b>50</b>	13.2	7.8	5.9	1.07
<b>60</b>	9.	6.5	4.9	0.79
<b>70</b>	6.4	5.6	4.2	0.62
<b>80</b>	4.8	4.9	3.7	0.5
<b>90</b>	4	4.3	3.3	0.42
<b>100</b>	3.5	3.9	2.9	0.36
<b>110</b>	3.3	3.6	2.7	0.31
<b>120</b>	3.5	3.3	2.4	0.27
<b>130</b>	3.8	3.0	2.3	0.24

<b>140</b>	4.3	2.8	2.1	0.22
<b>150</b>	4.9	2.6	2.0	0.2
<b>160</b>	5.6	2.4	1.8	0.18
<b>170</b>	6.4	2.3	1.7	0.17
<b>180</b>	7.3	2.2	1.6	0.15
<b>190</b>	8.2	2.1	1.5	0.14
<b>200</b>	9.2	2.0	1.5	0.13
<b>210</b>	10.2	1.9	1.4	0.13
<b>220</b>	11.3	1.8	1.3	0.12
<b>Listed values may differ slightly</b>	<b>*Without front cap</b>			<b>Unit = mm</b>

## Especificación

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x960)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 11.1 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF (max 1.3MP)
Supported image formats (MacOS)	JPEG, PNG

Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
<b>Housing</b>	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.3cm (D)
Weight	90g
Cable length	1.5m
<b>Features</b>	
Special feature	Flexible LED Control (FLC) & Automatic Magnification Reading (AMR)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover box with N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€900,00 - €1100,00

## Product Gallery

