

# AM8117MZTL



**Marque:**

**Code produit:** AM8117MZTL Edge Plus

## Courte description

High Optical Resolution

8.0 Megapixel

Enhanced Flexible LED Control (eFLC)

Long Working Distance

Robust Metal Housing

## Description

The AM8117MZTL 8-megapixel long working distance digital microscope captures images with stunning clarity and sharpness. Its advanced sensor technology, combined with the eFLC feature and adjustable polarizer, make the AM8117MZTL a reliable tool for high-quality imaging,



Metal  
housing



Enhanced Flexible  
LED control



Adjustable  
~10x - 140x



8,0 Megapixels  
3840 x 2160



Measurement  
functionality



8 White LEDs  
switchable



## The main features of the AM8117MZTL are:

- 8 Megapixels
- High Optical Resolution
- Enhanced Flexible LED Control (eFLC)
- Long Working Distance (LWD) Optics
- Adjustable Polarizer
- Robust Metal Housing
- 10x ~ 140x magnification (Edge shading occurs below 25x when previewing in 16:9 windows.)
- And more...

### Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	238.3	60.69	34.14	25.99
20	115.4	30.35	17.07	6.94
30	75.9	20.23	11.38	3.29
40	57.1	15.17	8.53	1.98
50	46.7	12.14	6.83	1.35
60	40.5	10.11	5.69	0.99
70	36.7	8.67	4.88	0.77
80	34.3	7.59	4.27	0.62
90	32.9	6.74	3.79	0.52
100	32.3	6.07	3.41	0.44
110	32.1	5.52	3.10	0.38
120	32.3	5.06	2.85	0.33
130	32.8	4.67	2.63	0.30
140	33.5	4.34	2.44	0.27

Listed values may differ slightly \* Without front cap

Unit = mm

### Spécification

Lighting	
Light/ LED type	White
Number of LEDs	8
Optics	

Magnification	10x ~ 140x
Working distance	238.3 ~ 33.5 mm
<b>Sensor</b>	
Sensor type	CMOS
Resolution	8.0 Megapixel (3840x2160)
Maximum frame rate	10 fps at 8.0 MP, MJPEG 25 fps at 2.0 MP, MJPEG
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 10/11
Supported image formats (Windows)	BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Supported video formats (Windows)	WMV, FLV, SWF
<b>Housing</b>	
Housing material	Metal housing
Dimensions	130 mm (H) x 33 mm (D)
Weight	120 g
<b>Features</b>	
Special feature	Auto and Manual Refocus
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
<b>Information</b>	
Package contents	N3C-C (Close Cap) N3C-D (Diffuser Cap) N3C-D2 (Opal Diffuser Cap) N3C-E (Extended Open Cap) N3C-L (Long Cap) N3C-O (Open Cap) N3C-S (Sidelight Cap)
Warranty information	2 years European warranty
Regulatory approval:	CE, FCC, ROHS
Price range	€1149,00 - €1349,00