

# AM4113ZTL




**Marca:**  
**Codice del prodotto:** AM4113ZTL

## Short Description

1.3 Megapixel resolution  
With magnification lock  
10x ~ 90x Magnification and Long working distance  
Polarizer (anti-reflection)

## Descrizione

By using a special polarization filter, the AM4113ZTL is the right choice when working with high glare materials such as plastics and metals. This model also has a long working distance.



**Working distance/field of view/depth of field**

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
<b>20</b>	151.0	19.6	15.6	
<b>30</b>	101.0	13.0	10.4	3.4
<b>40</b>	77.2	9.8	7.8	2.2
<b>50</b>	64.1	7.8	6.3	1.65
<b>60</b>	56.2	6.5	5.2	.
<b>70</b>	51.3	5.6	4.5	.
<b>80</b>	48.3	4.9	3.9	.
<b>90</b>	46.6	4.3	3.5	0.8

Listed values  
may differ  
slightly

Unit = mm

### Specifiche

<b>Lighting</b>	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	No
Polarizer	Yes, linear
<b>Optics</b>	
Magnification	10x ~ 90x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
<b>Sensor</b>	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats	JPEG, PNG

(MacOS)	
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
<b>Housing</b>	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	105g
Cable length	1.8m
<b>Features</b>	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, ZT-Z-CC1 cap closure, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€400,00 - €600,00