

# AM4917MZT4



**Marca:**

**Codice del prodotto:** AM4917MZT4

## Short Description

1.3 Megapixels

Extended Depth of Field (EDOF)

Extended Dynamic Range (EDR)

Automatic Magnification Reading (AMR)

Enhanced Flexible LED Control (eFLC)

## Descrizione

As magnification increases, targets with uneven surfaces are often out of focus due to the limited depth of field. AM4917MZT4 400x digital microscope eases focusing with its click-to-focus functionality and can generate focused-stacked images with EDOF.

Delivering superior images, equipped with a polarizer, and featuring EDOF, DPQ, AMR, and EDR, AM4917MZT4 is a quality imaging tool ready for a wide range of applications.

**Note: EDOF, EDR, and DPQ are available on Windows PC only.**




Extended  
Depth Of Field  
EDOF



Extended  
Dynamic  
Range EDR



Automatic  
Magnification  
Reading (AMR)




---

### The main features of the AM4917MT8 are:

- 1.3 Megapixels
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- Automatic Magnification Reading (AMR)
- Enhanced Flexible LED Control (eFLC)
- Integrated polarizer (anti-reflection)
- 400x-470x magnification
- And more...

*(\*EDOF/EDR only functions under Windows OS)*

### Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
400	5.68	0.977	0.732	0.041
410	6.63	0.953	0.715	0.040
420	7.59	0.93	0.698	0.039
430	8.55	0.909	0.681	0.038
440	9.51	0.888	0.666	0.038
450	9.62	0.868	0.651	0.037
460	9.56	0.849	0.637	0.036
470	9.50	0.831	0.623	0.036

Listed values may differ slightly \* Without front cap

Unit = mm

### Specifiche

Lighting	
Light/ LED type	White
Number of LEDs	8

<b>Optics</b>	
Magnification	400x ~ 470x
<b>Sensor</b>	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x960)
Maximum frame rate	30 fps in 1.3 MP, MJPEG 30 fps in VGA, MJPEG
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.12 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	PNG, JPEG
Supported video formats (MacOS)	MOV
<b>Housing</b>	
Housing material	Metal housing
Dimensions	10.7 cm (H) x 3.3 cm (D)
Weight	130 g
<b>Features</b>	
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
<b>Information</b>	
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1200,00 - €1400,00