

# AM7115MZT

**Marca:**

**Codice del prodotto:** AM7115MZT - EDGE



## Short Description

5 Megapixel resolution

Robust metal housing

10-220x magnification

Polarizer

Flexible LED Control (FLC)

## Descrizione

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features such as Flexible LED Control (FLC) and full aluminum body, the Dino-Lite AM7115MZT is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite AM7115MZT offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Measurement  
functionality



ADJUSTABLE  
~10-220x



Magnification  
lock



Metal  
housing



5 megapixel  
2592 x 1944




8 White LEDs  
switchable

Flexible LED  
Control FLC



Standard working  
distance



Exchangeable  
cap



Polarizer  
anti-reflection

The AM7115MZT is part of the universal range and with its standard working distance and wide magnification range from 10 – 220x, it is suitable for a wide range of applications. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

### The main features of the AM7115MZT are:

- 5 Megapixel Edge sensor
- 10-220x magnification
- Integrated polarizer
- Aluminum housing
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- And more...

### Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE 1	WORKING DISTANCE 2*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>		<b>* Without front cap</b>			<b>Unit = mm</b>
10	-	142.6	39.6	29.7	2.6
20	52.7	60.1	19.5	15.6	2.5
30	26.0	33.5	13.0	10.4	1.8
40	13.4	20.9	9.8	7.8	1.5
50	6.4	13.9	7.8	6.3	-
60	2.2	9.7	6.5	5.2	-
70	-	7.1	5.6	4.5	1.0
80	-	5.5	4.9	3.9	-
90	-	4.5	4.3	3.5	-

100	-	4.1	3.9	3.1	-
110	-	4.0	3.6	2.8	-
120	-	4.1	3.3	2.6	-
130	-	4.5	3.0	2.4	-
140	-	5.0	2.8	2.2	-
150	-	5.6	2.6	2.1	-
160	-	6.3	2.4	2.0	-
170	-	7.1	2.3	1.8	-
180	-	8.0	2.2	1.7	-
190	-	8.9	2.1	1.6	-
200	-	9.9	2.0	1.6	-
210	-	10.9	1.9	1.5	-
220	-	11.9	1.8	1.4	0.1

## Specifiche

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	5.0 Megapixel (2592x1944)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats	JPEG, PNG

(MacOS)	
Supported video formats (MacOS)	MOV (max 1.3MP)
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
<b>Housing</b>	
Housing material	Metal housing
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	135gr
Cable length	1.8m
<b>Features</b>	
Special feature	Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3c-extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years EuNoropean warranty
Regulatory approval	CE, FCC, ROHS
Price range	€750,00 - €1000,00

## Product Gallery



