

# AM73915MZTL



**Marca:**

**Codice del prodotto:** AM73915MZTL

## Short Description


5 Megapixel Edge sensor  
USB 3.0, maximum 45fps  
10-140x magnification  
Long working distance  
Flexible LED Control (FLC)  
Polarizer  
Extended Depth of Field (EDOF)  
Extended Dynamic Range (EDR)  
Automatic Magnification Reading (AMR)

## Descrizione

The Dino-Lite AM73915MZTL is a Long Working Distance model that is part of the High Speed range with USB 3.0 connection. It offers superb uncompressed image quality and color reproduction in a robust, compact and appealing metal housing.

USB 3.0 adds a new transfer mode called "SuperSpeed" (SS) capable of transferring data up to 5Gbits/s (625MB/s). Dino-Lite models with USB 3.0 offer an image transfer speed of up to 45FPS at a 1280 x 960 resolution. SuperSpeed allows you to take advantage of the full power of the Dino-Lite Edge Series optics including improved colour accuracy and image quality.

---



EDOF allows users to automatically capture multiple images at different depths and automatically combine them into one clear image. EDR automatically captures and combines multiple images at different exposure levels to produce a final image with greater dynamic range. The AMR function automatically detects and displays the magnification of the Dino-Lite. The magnification is displayed within the Dino-Lite software and stored with the captured picture and simplifies the measuring process.

The AM73915MZTL is one top-level Dino-Lite products available and the most advanced product within the Dino-Lite USB 3.0 range. For professionals who are looking for extended working distance, high speed data transfer, the best available image quality and many advanced features this is the model of choice.

The Dino-Lite AM73915MZTL is a USB 3.0 model with a magnification range of 10x - 140x and a Long Working Distance of up to 24 cm. This model is member of the Dino-Lite Edge family with the latest, cutting-edge optics, an unmatched 5 megapixel sensor and several special features such as the Extended Depth of Field (EDOF), Enhanced Dynamic Range (EDR), Automatic Magnification Reading (AMR), Flexible LED Control (FLC), built-in polarization filter, full metal body, extensive measurement functions, calibration, exchangeable front caps and more.

***\*EDOF/EDR only functions under Windows OS***

## Optical Data Table

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE*</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
<b>10</b>	234.5	39.0	29.2	12.0
<b>20</b>	112.5	19.5	14.6	4.5
<b>30</b>	72.5	13.0	9.7	3.1
<b>40</b>	54.5	9.8	7.3	1.8
<b>50</b>	43.5	7.8	5.8	1.2
<b>60</b>	37.5	6.5	4.8	0.9
<b>70</b>	33.7	5.6	4.2	0.6
<b>80</b>	31.3	4.9	3.6	0.5
<b>90</b>	29.9	4.3	3.2	0.37
<b>100</b>	29.2	3.9	2.9	0.28
<b>110</b>	29.1	3.5	2.6	0.22
<b>120</b>	29.3	3.3	2.4	0.17
<b>130</b>	29.8	3.0	2.2	0.12
<b>140</b>	30.5	2.8	2.1	0.09

**Listed values may differ slightly**      **\*Without front cap**      **Unit = mm**

## Specifiche

<b>Lighting</b>	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
<b>Optics</b>	
Magnification	10x ~ 140x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
<b>Sensor</b>	
Sensor type	CMOS
Resolution	5 Megapixel (2592x1944)
Maximum frame rate	45fps (max 20fps video recording)

Compatibility	
Interface	USB 3.0, Cable included**
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV (max 1.3MP)
Imaging standards	DirectShow, UVC
Wifi	No
Housing	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	11.9cm (L) x 3.3cm (H)
Weight	110g
Cable length	1.8m
Features	
Special feature	Automatic Magnification Reading (AMR), Extended Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC).
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
Information	
Package contents	Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1300,00 - €1500,00
Note	**Dino-Lite USB 3.0 models use a custom USB-A and USB-C cable that is specifically designed for Dino-Lite

## Product Gallery

