

# AF4535ZTE

**Marca:**

**Codice del prodotto:** AF4535ZTE


## Short Description

1.3 Megapixel Edge sensor  
10x~330x magnification  
Adjustable polarizer  
Flexible LED Control (FLC)  
Automatic Magnification Reading (AMR)

## Descrizione

The Dino-Lite AF4535ZTE is part of Universal series and connects to your device via USB. The AF4535ZTE is Wireless-ready, but requires the (optional) WF-20 to make it a fully wireless solution.

In comparison, the AF4x35 series provides a similar working distance range but achieves higher magnifications compared to the AM4x15 series.



---

The AF4535ZTE is equipped with premium features such as Flexible LED control (FLC), integrated polarizer, extensive measurement functionality and Automatic Magnification Reading (AMR) for measurement-intensive applications.

## The main features of the AF4535ZTE are:

- Wireless-ready, requires the WF-20 adapter (optional)
- 10x~330x magnification

- 1.3 Megapixel Edge sensor
- Adjustable polarizer
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- And more...

**Working distance/field of view/depth of field**

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE *</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
10	98.9	19.5	14.7	14.6
30	58.5	13.0	9.8	6.8
40	38.7	9.8	7.3	4.0
50	27.2	7.8	5.9	2.7
60	19.9	6.5	4.9	2.0
70	14.9	5.6	4.2	1.5
80	11.5	4.9	3.7	1.2
90	9.0	4.3	3.3	1.0
100	7.2	3.9	2.9	0.8
110	5.9	3.6	2.7	0.7
120	4.9	3.3	2.4	0.6
130	4.3	3.0	2.3	0.5
140	3.9	2.8	2.1	0.5
150	3.7	2.6	2.0	0.4
160	3.6	2.4	1.8	0.4
170	3.7	2.3	1.7	0.4
180	3.8	2.2	1.6	0.3
190	4.1	2.1	1.5	0.3
200	4.4	2.0	1.5	0.3
210	4.7	1.9	1.4	0.3
220	5.2	1.8	1.3	0.2
230	5.6	1.7	1.3	0.2
240	6.2	1.6	1.2	0.2
250	6.7	1.6	1.2	0.2
260	7.3	1.5	1.1	0.2
270	7.9	1.4	1.1	0.2
280	8.5	1.4	1.0	0.2
290	9.2	1.3	1.0	0.2
300	9.9	1.3	1.0	0.2
310	10.6	1.3	0.9	0.2
320	11.3	1.2	0.9	0.1
330	12.0	1.2	0.9	0.1

Listed values  
may differ  
slightly

\* Without front  
cap

Unit = mm

## Specifiche

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x~330x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.12 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 adapter (optional)
Housing	

Housing material	Composite/ plastic housing
Dimensions	11.4cm (L) x 3.3cm (D)
Weight	111g
Cable length	1.8m
<b>Features</b>	
Special feature	Automatic Magnification Reading (AMR), Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, Carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€550,00 - €750,00

## **Product Gallery**