

AM4113ZTL



Merk:
Productcode: AM4113ZTL

Korte omschrijving

1.3 Megapixel resolution
With magnification lock
10x ~ 90x Magnification and Long working distance
Polarizer (anti-reflection)

Omschrijving

By using a special polarization filter, the AM4113ZTL is the right choice when working with high glare materials such as plastics and metals. This model also has a long working distance.



USB 2.0



Measurement
functionality



CONTINUOUS
~20x-90x



1,3 Megapixels
1280 x 1024



8 White LEDs
switchable



Magnification
lock



Long working
distance



Polarizer
anti-reflection

Working distance/field of view/depth of field

MAGNIFICATI WORKING ON RATE	DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	151.0	19.6	15.6	
30	101.0	13.0	10.4	3.4
40	77.2	9.8	7.8	2.2
50	64.1	7.8	6.3	1.65
60	56.2	6.5	5.2	.
70	51.3	5.6	4.5	.
80	48.3	4.9	3.9	.
90	46.6	4.3	3.5	0.8

Listed values may differ slightly

Unit = mm

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	No
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Magnification	10x ~ 90x
Macro zoom	No
Werkafstand	Long
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde	JPEG, PNG

beeldformaten (MacOS)	
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Vergrotingsslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)
Gewicht	105g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	No
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, ZT-Z-CC1 cap closure, user manual
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€400,00 - €600,00