

# AM4115-FUT - EDGE

**Merk:**

**Productcode:** AM4115-FUT - EDGE



## Korte omschrijving

1.3 Megapixel resolution

Versatility due to exchangeable caps

~375nm UV LEDs

20-220x magnification

## Omschrijving

The AM4115-FUT has special lighting with LED's emitting UV light around the 375 nm spectrum.



USB 2.0



Measurement  
functionality



Adjustable  
~20x-220x



Magnification  
lock



1.3 megapixel  
1280 x 1024



UV-LEDs  
375 nm



Exchangeable  
cap



Standard working  
distance


The Dino-Lite Edge models provide superior image quality and a high level of flexibility due to the adaptable cap design.

» Also available with 390-400nm LEDs (model AM4115-FVT).

**Working distance/field of view/depth of field**

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
<b>Listed values may differ slightly</b>	<b>* Without front cap</b>			<b>Unit = mm</b>
20	60.2	19.5	15.6	2.5
30	33.5	13.0	10.4	1.8
40	20.9	9.8	7.8	1.5
50	13.9	7.8	6.3	-
60	9.7	6.5	5.2	-
70	7.1	5.6	4.5	1.0
80	5.5	4.9	3.9	-
90	4.5	4.3	3.5	-
100	4.1	3.9	3.1	-
110	4.0	3.6	2.8	-
120	4.1	3.3	2.6	-
130	4.5	3.0	2.4	-
140	5.0	2.8	2.2	-
150	5.6	2.6	2.1	-
160	6.3	2.4	2.0	-
170	7.1	2.3	1.8	-
180	8.0	2.2	1.7	-
190	8.9	2.1	1.6	-
200	9.9	2.0	1.6	-
210	10.9	1.9	1.5	-
220	11.9	1.8	1.4	0.1

**Special Light**



## Specificatie

Verlichting	
Licht / LED-type	~375nm UV
Aantal leds	4
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	Yes, Emission barrier filter 375 nm
Polarisator	No
Optiek	
Magnification	20x ~ 220x
Macro zoom	No
Werkafstand	Standard
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	1.3 Megapixel (1280x1024)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Behuizing	
Materiaal van de behuizing	Composite/ plastic housing
Vergrotingslot	Yes
Afmetingen	10.5cm (L) x 3.2cm (D)
Gewicht	100g
Kabellengte	1.8m
Kenmerken	

Bijzonderheid	No
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	No
<b>Informatie</b>	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€500,00 - €700,00

## Product galerij

