

AM8517MZTL

Merk: Dino-Lite

Productcode: AM8517MZTL Edge Plus



Korte omschrijving

High Optical Resolution

8.0 Megapixel

Enhanced Flexible LED Control (eFLC)

Automatic Magnification Reading (AMR)

Long Working Distance

Omschrijving

Capture stunning images with the AM8517MZTL 8-megapixel long working distance digital microscope. Engineered with a comprehensive set of features, including AMR, this model is designed to excel in both imaging and measurement-oriented tasks.



Metal housing



Enhanced Flexible LED control



Adjustable
~10x - 140x




8,0 Megapixels
3840 x 2160



Measurement functionality



8 White LEDs
switchable



Polarizer
anti-reflection



Automatic
Magnification
Reading (AMR)



Long working
distance

The main features of the AM8517MZTL are:

- 8 Megapixels
- High Optical Resolution
- Automatic Magnification Reading (AMR)
- Enhanced Flexible LED Control (eFLC)
- Long Working Distance (LWD) Optics
- Adjustable Polarizer
- Robust Metal Housing
- 10x ~ 140x magnification (Edge shading occurs below 25x when previewing in 16:9 windows.)
- And more...

Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	238.3	60.69	34.14	25.99
20	115.4	30.35	17.07	6.94
30	75.9	20.23	11.38	3.29
40	57.1	15.17	8.53	2.00
50	46.7	12.14	6.83	1.42
60	40.5	10.11	5.69	1.09
70	36.7	8.67	4.88	0.87
80	34.3	7.59	4.27	0.72
90	32.9	6.74	3.79	0.62
100	32.3	6.07	3.41	0.53
110	32.1	5.52	3.10	0.47
120	32.3	5.06	2.85	0.42
130	32.8	4.67	2.63	0.38
140	33.5	4.34	2.44	0.35

Listed values may differ slightly * Without front cap

Unit = mm

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
Optiek	
Magnification	10x ~ 140x
Werkafstand	238.3 ~ 33.5 mm
Sensor	
Sensortype	CMOS
Resolutie	8 Megapixel (3840 x 2160)

Maximale framesnelheid	10 fps at 8.0 MP, MJPEG 25 fps at 2.0 MP, MJPEG
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 10/11
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Behuizing	
Materiaal van de behuizing	Metal housing
Afmetingen	130 mm (H) x 33 mm (D)
Gewicht	120 g
Kenmerken	
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
Informatie	
Inhoud van de verpakking	N3C-C (Close Cap) N3C-D (Diffuser Cap) N3C-D2 (Opal Diffuser Cap) N3C-E (Extended Open Cap) N3C-L (Long Cap) N3C-O (Open Cap) N3C-S (Sidelight Cap)
Garantie-informatie	2 years European warranty
Regulatory approval:	CE, FCC, ROHS
Prijsklasse	€1200,00 - €1400,00