

# N3C-A



**Merk:** Dino-Lite  
**Productcode:** N3C-A

## **Korte omschrijving**

Coaxial Light Cap

## **Omschrijving**

The N3C-A coaxial light cap is a useful accessory for the Dino-Lite Edge models from the Long Working Distance range. Especially difficult to inspect surfaces such as metal, plastics or glass benefit from this addition.

Inside the small and light front cap an ingenious mirroring system with a beam splitter has been integrated. The combination of coaxial lighting, a high sensitive camera and a magnification of up to 140 times makes it possible to visualize even the smallest scratches and dents on any surface. The coaxial lighting does also eliminate disturbing shadows making it easier to look inside small holes in the material you wish to check.

The NC3-A coaxial light cap is interchangeable with other caps from the Dino-Lite range. The optimum result can be achieved by using it in combination with a Dino-Lite Edge model from the Long Working Distance range (LWD).

## **Specificatie**

| Compatibiliteit |   |
|-----------------|---|
| Compatibel met: | All Long Working Distance Edge models (AM4x15, AM4xx17, AM5216, AM5218, |

|                          |   |
|--------------------------|---|
|                          | AM7x15, AM73xx15, type TL/ZTL)*   |
| <b>Behuizing</b>         |   |
| Afmetingen               | 18.5mm (H) x 30.3mm (D)   |
| Gewicht                  | 6 g   |
| <b>Kenmerken</b>         |   |
| ESD veilig               | No  |
| <b>Informatie</b>        |   |
| Inhoud van de verpakking | N3C-A coaxial light cap, Quick start guide  |
| Garantie-informatie      | 2 years European warranty   |
| accessoires:             | Light and control   |
| Prijsklasse              | €100,00 - €200,00   |
| Note                     | *The working distance of Dino-Lite attached with N3C-A will be reduced by 5mm. Some magnification range of standard working distance models could thus be obscured from using. Standard working distance models may function with N3C-A at 225x or less than 50 |

## Product galerij



