

PH-F1 SET

Merk: Photonic

Productcode: 10030 + 595-20-167

Korte omschrijving

Fiber optic illumination, LED

Fiber optic light guide: Double-arm goose-neck

High power cold light source, metal housing

Adjustable brightness control

Omschrijving

Fibre-optic lighting systems consist of a light source and a fibre-optic light guide. By using fibre optics the sample is not effected by any warmth at all.

The Photonic F1-set is composed of the F1 LED cold light source and the fiberoptic light guide with a double arm gooseneck. The sturdy metal housing of the F1 is ESD safe and has a control knob to adjust the brightness of the illumination. The fiberoptic light guide with the double arm gooseneck can be easily adjusted to provide the best angle of illumination to your sample.

** All other Photonic items are also available through Dino-Lite Europe.*

Specificatie

Compatibiliteit	
Compatibel met:	All Dino-Lite models, except high magnification models
Behuizing	
Afmetingen	96x110x175mm (unit) 55cm (gooseneck)
Gewicht	2500 g (unit) / 550 g (gooseneck)
Kenmerken	
ESD veilig	Yes
Informatie	
Inhoud van de verpakking	F1 (10030) LED Cold light source with power supply with EU & UK plug and double arm gooseneck (595-20-167) ESD Safe add-ons not included

Garantie-informatie	2 years European warranty
accessoires:	Light and control
Prijsklasse	€550,00 - €650,00

Product galerij

