

MSAK810



Merk: Dino-Lite
Productcode: MSAK810

Korte omschrijving

Flexible extension arm

Omschrijving

The MSAK810 adjustable flex arm which can be attached to the pole of a RK-06A/RK-06AE/RK-06F for additional hands free viewing angles with the Dino-Lite. The arm has a maximum of 30cm reach, and can be bent and twisted to attain your desired viewing positions.

The MSAK810 is a great addition to a RK-06A/RK-06AE/RK-06F allowing an in-depth visual inspection with multiple Dino-Lite's.

Specificatie

| | |
|--------------------------|------------------------|
| Compatibiliteit | |
| Compatibel met: | All Dino-Lite models |
| Behuizing | |
| Afmetingen | 35.5cm (W) x 3.1cm (L) |
| Gewicht | 181 g |
| Kenmerken | |
| ESD veilig | No |
| Informatie | |
| Inhoud van de verpakking | Stand, HD-P1 holder |

| | |
|---------------------|---------------------------|
| Garantie-informatie | 2 years European warranty |
| accessoires: | Professional stands |
| Prijsklasse | €50,00 - €150,00 |

Product galerij

