

AM73115MZTL



Merk:

Productcode: AM73115MZTL

Korte omschrijving

5 Megapixel Edge sensor

USB 3.0, maximum 45fps

10-140x magnification

Long working distance (3,5~24cm)

Flexible LED Control (FLC)

Polarizer

Omschrijving

With the use of the USB 3.0 connection the AM73115MZTL is able to capture smooth and high-quality images. The Edge series optics and the special feature Flexible LED Control (FLC) makes the AM73115MZTL the best choice for the more demanding applications



USB 3.0



High speed



Adjustable
~10x - 140x



Measurement
functionality



Magnification
lock



5 megapixel
2592 x 1944



The AM73115MZTL is part of the high speed range due to its USB 3.0 connection with a maximum speed of 45fps at 1280x960 and 15fps at 2560x1920. With its magnification range from 10 – 140x and long working distance, it is suitable for a broad range of applications. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the AM73115MZTL are:

- 5 Megapixel Edge sensor
- USB 3.0 with up to 45fps
- 10-140x magnification
- Long working distance
- Integrated polarizer
- Aluminum housing
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- And more...

Optical Data Table

Magnification Rate	Working Distance *	Field of View(x)	Field of View(y)	Depth of Field
10	234.5	39.0	29.2	12.0
20	112.5	19.5	14.6	4.5
30	72.5	13.0	9.7	3.1
40	54.5	9.8	7.3	1.8
50	43.5	7.8	5.8	1.2
60	37.5	6.5	4.8	0.9
70	33.7	5.6	4.2	0.6
80	31.3	4.9	3.6	0.5
90	29.9	4.3	3.2	0.37
100	29.2	3.9	2.9	0.28
110	29.1	3.5	2.6	0.22

120	29.3	3.3	2.4	0.17
130	29.8	3.0	2.2	0.12
140	30.5	2.8	2.1	0.09
Listed values may differ slightly	* Without front cap			Unit = mm

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Magnification	10x ~ 140x
Macro zoom	No
Werkafstand	Long
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	5 Megapixel (2560x1920)
Maximale framesnelheid	45fps (max 20fps video recording)
Compatibiliteit	
Interface	USB 3.0, Cable included**
Besturingssysteem	Windows7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	JPEG, PNG
Ondersteunde videoformaten (MacOS)	MOV (max 1.3MP)
Beeldvormingsnormen	DirectShow, UVC

Wifi	No
Behuizing	
Materiaal van de behuizing	Metal housing
Vergrotingsslot	Yes
Afmetingen	11.9cm (L) x 3.3cm (H)
Gewicht	110g
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Flexible LED Control (FLC)
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	Yes
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€1000,00 - €1200,00
Note	**Dino-Lite USB 3.0 models use a custom USB-A and USB-C cable that is specifically designed for Dino-Lite

Product galerij