

AF7515MZTL - EDGE



Merk:

Productcode: AF7515MZTL

Korte omschrijving

High Optical Resolution

5-Megapixels

Long Working Distance (LWD) Optics

Flexible LED Control (FLC)

Adjustable Polarizer

Omschrijving

The 5-megapixel AF7515MZTL digital microscope provides a long working distance solution for capturing high-resolution images. Equipped with AMR and FLC, AF7515MZTL is a powerful tool for facilitating measurements and obtaining high-quality images. This model is compatible with the WF-20 Wi-Fi streamer.



USB 2.0



Flexible LED
Control FLC



Continuous
~10x - 140x



Measurement
functionality



Metal
housing



5 megapixel
2592 x 1944



Automatic
Magnification
Reading (AMR)



Magnification
lock



Polarizer
anti-reflection



Exchangeable
cap

Wireless
Ready

The AF7515MZTL is part of the Long Working Distance (LWD) range and with its Long Working Distance and magnification range from 10 – 140x, it is suitable for a wide range of applications where extra distance to the object or a larger field of view is required.

The extra working distance and larger field of view make this model an ideal solution for tasks such as repair, rework or assembly or for working with bulky or fragile objects that cannot be touched. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc. The AMR function is of particular importance when the measurement functions are frequently used.

The main features of the AF7515MZTL are:

- 5 Megapixel Edge sensor
- Long Working Distance (LWD)
- 10-140x magnification
- Integrated polarizer
- Aluminum housing
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- Wireless ready
- And more...

Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
Listed values may differ slightly	* Without front cap			Unit = mm
10	237.5	39.6	29.7	25.8

20	115.3	19.8	14.8	6.9
30	75.9	13.2	9.9	3.3
40	57.3	9.9	7.4	2.2
50	47.0	7.9	5.9	1.6
60	40.8	6.6	4.9	1.2
70	36.9	5.7	4.2	1.0
80	34.6	4.9	3.7	0.8
90	33.2	4.4	3.3	0.7
100	32.6	4.0	3.0	0.6
110	32.4	3.6	2.7	0.5
120	32.6	3.3	2.5	0.5
130	33.1	3.0	2.3	0.4
140	33.8	2.8	2.1	0.4

Specificatie

Verlichting	
Licht / LED-type	White
Aantal leds	8
LED aan / uit schakelbaar:	Yes
Infrarood filter	IR cut-filter >650 nm
Diffusor beschikbaar	Yes (N3C-D included)
Emissiefilter	No
Polarisator	Yes, linear
Optiek	
Magnification	10x ~ 140x
Macro zoom	No
Werkafstand	Long
Type lens	Glass with anti-reflection coating
Sensor	
Sensortype	CMOS
Resolutie	5 Megapixel (2592x1944)
Maximale framesnelheid	30 fps
Compatibiliteit	
Interface	USB 2.0
Besturingssysteem	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Ondersteunde beeldformaten (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Ondersteunde videoformaten (Windows)	WMV, FLV, SWF
Ondersteunde	JPEG, PNG

beeldformaten (MacOS)	
Ondersteunde videoformaten (MacOS)	MOV (max 1.3MP)
Beeldvormingsnormen	DirectShow, UVC
Wifi	Wireless-ready, requires the WF- 20 (optional)
Behuizing	
Materiaal van de behuizing	Metal housing
Vergrotingsslot	Yes
Afmetingen	11.5cm (L) x 3.4cm (D)
Gewicht	97gr
Kabellengte	1.8m
Kenmerken	
Bijzonderheid	Automatic Magnification Reading (AMR), Flexible LED Control (FLC).
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
ESD veilig	Yes
Informatie	
Inhoud van de verpakking	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS
Prijsklasse	€1000,00 - €1200,00