

# AM8917MT8A

## Merk:

**Productcode:** AM8917MT8A

## Korte omschrijving

8.0 Megapixel

Enhanced Flexible LED Control (eFLC, with coaxial light)

Depth Acquisition (DPQ)

Extended Depth of Field (EDOF)

Automatic Magnification Readout (AMR)

## Omschrijving

Equipped with coaxial light, EDOF, and many other sophisticated features, AM8917MT8A is an 800x microscope ideal for viewing reflective surfaces and delivering all-in-focus images. The AM8917MT8A includes DPQ, EDR, AMR, and Auto and Manual Refocusing.

## Working distance/field of view/depth of field

M	WD	FOV (x)	FOV (y)	DOF
700	5.8	0.87	0.49	0.01
750	5.7	0.81	0.46	0.01
800	5.6	0.76	0.43	0.01
850	5.6	0.71	0.40	0.01
900	5.5	0.68	0.38	0.01

## Specificatie

Verlichting	
Licht / LED-type	White LED
Optiek	
Magnification	700x ~ 900x
Sensor	
Resolutie	8.0 Megapixel (3840 x 2160)
Maximale framesnelheid	10 fps at 8.0 MP, MJPEG 25 fps at 2.0 MP, MJPEG
Compatibiliteit	
Interface	USB 2.0

Besturingssysteem	Windows 10/11 macOS 10.14 or later
Ondersteunde beeldformaten (Windows)	DinoCapture 2.0: BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Ondersteunde videoformaten (Windows)	DinoCapture 2.0: WMV, FLV, SWF
Ondersteunde beeldformaten (MacOS)	DinoXcope: PNG, JPEG
Ondersteunde videoformaten (MacOS)	DinoXcope: MOV
<b>Behuizing</b>	
Vergrotingsslot	Yes
Afmetingen	133 mm (H) x 32 mm (D)
Gewicht	Approx. 124 g
Kabellengte	Approx. 1.8 m
<b>Kenmerken</b>	
Meting	Yes
Kalibratie	Yes
Microtouch-sensor	Yes
<b>Informatie</b>	
Inhoud van de verpakking	Microscope, carry pouch, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Garantie-informatie	2 years European warranty
Regelgevende goedkeuring	CE, FCC, ROHS