

PH-F1 SET

Brand:

Product Code: 10030 + 595-20-167

Short Description

Fiber optic illumination, LED

Fiber optic light guide: Double-arm goose-neck

High power cold light source, metal housing

Adjustable brightness control

Description

Fibre-optic lighting systems consist of a light source and a fibre-optic light guide. By using fibre optics the sample is not effected by any warmth at all.

The Photonic F1-set is composed of the F1 LED cold light source and the fiberoptic light guide with a double arm gooseneck. The sturdy metal housing of the F1 is ESD safe and has a control knob to adjust the brightness of the illumination. The fiberoptic light guide with the double arm gooseneck can be easily adjusted to provide the best angle of illumination to your sample.

** All other Photonic items are also available through Dino-Lite Europe.*

Specification

| Compatibility | |
|------------------|--|
| Compatible with: | All Dino-Lite models, except high magnification models |
| Housing | |
| Dimensions | 96x110x175mm (unit) 55cm (gooseneck) |
| Weight | 2500 g (unit) / 550 g (gooseneck) |
| Features | |
| ESD safe | Yes |
| Information | |
| Package contents | F1 (10030) LED Cold light source with power supply with EU & UK plug and double arm gooseneck (595-20-167) ESD Safe add-ons not included |

| | |
|----------------------|---------------------------|
| Warranty information | 2 years European warranty |
| Accessory range: | Light and control |
| Price range | €800,00 - €900,00 |

Product Gallery

