

RK-10F / RK-10FS

Brand:

Product Code: RK-10F / RK-10FS



Short Description

Quick Release Button

Fine-Focus Knob

Anti-Backlash Lock

Arm Screw

HD-M2A

Description

The RK-10F is an upgraded version of the RK-10, featuring an improved quick release button with an anti-backlash mechanism that enhances its ability to make precise focus adjustments, ensuring smoother and more responsive operation.

The RK-10FS incorporates a heavier antistatic baseplate that suppresses external vibrations, making it an optimal choice for stable operation under high-magnification inspections.

[AVAILABLE EXTENSIONS FOR THE RK-10A STAND](#)

RK-10-EX



Additional horizontal arm (included with RK-10A)

RK-10-FX



Flexible arm extension

RK-10-VX



Vertical arm extension

RK-10-PX2



X and Y positioning arm

Specification

| | |
|------------|--------------------------------------|
| Housing | |
| Dimensions | 226 mm (H) x 150 mm (D) x 220 mm (L) |
| Dimensions | 226 mm (H) x 150 mm (D) x 220 mm (L) |
| Weight | Approx. 1050 g |
| Weight | Approx. 1900 g |
| Features | |
| ESD safe | Yes |

| Information | |
|----------------------|--|
| Package contents | Stand, HD-P1 holder, RK-10-EX horizontal arm |
| Warranty information | 2 years European warranty |
| Accessory range: | Professional stands |
| Price range | €300,00 - €450,00 |

Product Gallery

