

WF7515MZTL

Brand:

Product Code: WF7515MZTL



Short Description

5 Megapixel resolution
Robust metal housing
10-140x magnification
Long working distance
Flexible LED Control (FLC)
Polarizer
Automatic Magnification Reading (AMR)
Wireless

Description

With the use of the latest, cutting-edge optics, a brand new 5 megapixel sensor and several special features such as Flexible LED Control (FLC) and full aluminum body, the Dino-Lite WF7515MZTL is a marvel of technology and the best choice for the high-demanding professional. The Dino-Lite WF7515MZTL offers superb image quality and color reproduction in a robust, compact and appealing housing.



USB 2.0



Flexible LED
Control FLC



Continuous
~10x - 140x



The WF7515MZTL is part of the Long Working Distance (LWD) range and with its Long Working Distance and magnification range from 10 – 140x, it is suitable for a wide range of applications where extra distance to the object or a larger field of view is required.

The extra working distance and larger field of view make this model an ideal solution for tasks such as repair, rework or assembly or for working with bulky or fragile objects that cannot be touched. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc. The AMR function is of particular importance when the measurement functions are frequently used.

The main features of the WF7515MZTL are:

- 5 Megapixel Edge sensor
- Long Working Distance (LWD)
- 10-140x magnification
- Integrated polarizer
- Aluminum housing
- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Extensive measurement functions
- Calibration
- Exchangeable front caps
- Wireless
- And more...

Working distance/field of view/depth of field

| | | | | |
|----------------------|------------------------|------------------|------------------|------------------|
| MAGNIFICATION RATE | WORKING DISTANCE* | FIELD OF VIEW(X) | FIELD OF VIEW(Y) | DEPTH OF FIELD |
| Listed values | * Without front | | | Unit = mm |

**may differ
slightly**

cap

| | | | | |
|-----|-------|------|------|------|
| 10 | 234.5 | 39.0 | 31.2 | 12 |
| 20 | 112.5 | 19.5 | 15.6 | 4.5 |
| 30 | 72.5 | 13.0 | 10.4 | 3.1 |
| 40 | 54.5 | 9.8 | 7.8 | 1.8 |
| 50 | 43.5 | 7.8 | 6.2 | 1.2 |
| 60 | 37.5 | 6.5 | 5.2 | 0.9 |
| 70 | 33.7 | 5.6 | 4.5 | 0.6 |
| 80 | 31.3 | 4.9 | 3.9 | 0.5 |
| 90 | 29.9 | 4.3 | 3.5 | 0.37 |
| 100 | 29.2 | 3.9 | 3.1 | 0.28 |
| 110 | 29.1 | 3.5 | 2.8 | 0.22 |
| 120 | 29.3 | 3.3 | 2.6 | 0.17 |
| 130 | 29.8 | 3.0 | 2.4 | 0.12 |
| 140 | 30.5 | 2.8 | 2.2 | 0.09 |

Specification

| | |
|------------------------|-------------------------------------------------------------|
| Lighting | |
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | Yes (N3C-D included) |
| Emission filter | No |
| Polarizer | Yes, linear |
| Optics | |
| Magnification | 10x ~ 140x |
| Macro zoom | No |
| Working distance | Long |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 5.0 Megapixel (2592x1944) |
| Maximum frame rate | 30 fps |
| Compatibility | |
| Interface | USB 2.0 |
| Operating system | Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only) |

| | |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Software | DinoCapture 2.0 (Windows) cable + wireless, DinoXcope (Mac OS) cable only, DinoConnect wireless only |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF |
| Supported image formats (MacOS) | JPEG, PNG |
| Supported video formats (MacOS) | MOV (max 1.3MP) |
| Imaging standards | DirectShow, UVC |
| Wifi | Yes |
| Housing | |
| Housing material | Metal housing |
| Magnification lock | Yes |
| Dimensions | 10.5cm (L) x 3.2cm (D) |
| Weight | 135gr |
| Cable length | 1.8m |
| Features | |
| Special feature | Automatic Magnification Reading (AMR), Flexible LED Control (FLC). |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | Yes |
| Information | |
| Package contents | Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €1400,00 - €1600,00 |

Product Gallery

