

# AF7515MZT4

**Marka:** Dino-Lite  
**Ürün Kodu:** AF7515MZT4 - Edge



## Short Description

- 5 Megapixel resolution
- Robust metal housing
- Flexible LED Control (FLC)
- Automatic Magnification Reading (AMR)
- Adaptable Interface

## Açıklama

The 5MP Edge AF515MZT4 provides high-quality images with remarkable color performance at 400x magnification. With a built-in polarizer and FLC, the AF7515MZT4 is a versatile tool for a wide range of tasks, including viewing small defects, edge sharpness, and surface roughness. AF7515MZT4 features AMR to facilitate measurements and is also compatible with the optional WF-20 Wi-Fi streamer.



USB 2.0



Flexible LED Control FLC



Measurement functionality



Metal housing



5 megapixel  
2592 x 1944



8 White LEDs  
switchable



Magnification lock

Adjustable  
~400x-470x



Polarizer anti-reflection



Exchangeable cap

---

## The main features of the AF7515MZT - Edge are:

- 5 Megapixel Edge sensor
- High optical Resolution
- Automatic Magnification Reading
- Adjustable polarizer
- Robust Metal housing
- Flexible LED Control (FLC)
- Adaptable Interface
- And more...

### Working distance/field of view/depth of field

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
Listed values may differ slightly		<b>* Without front cap</b>		
				<b>Unit = mm</b>
400	4.8	0.99	0.74	0.040
410	5.8	0.97	0.72	0.039
420	6.7	0.94	0.71	0.038
430	7.7	0.92	0.69	0.037
440	8.6	0.90	0.67	0.036
450	8.6	0.88	0.66	0.035
460	8.5	0.86	0.65	0.034
450	8.4	0.84	0.63	0.034

### Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Diffuser available	Yes (N3C-D included)
Emission filter	No

Polarizer	Yes, linear
<b>Optics</b>	
Magnification	400x ~ 470x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
<b>Sensor</b>	
Sensor type	CMOS
Resolution	5 Megapixel (2592x1944)
Maximum frame rate	30 fps
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.14 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV (max 1.3MP)
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 WiFi streamer (optional)
<b>Housing</b>	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	11.5 cm (H) x 3.4 cm (D)
Weight	97g
Cable length	1.8m
<b>Features</b>	
Special feature	Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
<b>Information</b>	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E-

	extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€900,00 - €1100,00

## **Product Gallery**