

AF7915MZT



Marka:
Ürün Kodu: AF7915MZT

Short Description

5 Megapixel resolution
Extended Depth of Field (EDOF)
Extended Dynamic Range (EDR)
Flexible LED Control (FLC)
Automatic Magnification Reading (AMR)
Wireless Ready

Açıklama

Get the detail you need on the go with the Dino-Lite AF7915MZT high-resolution digital microscope. This 5-megapixel handheld digital microscope includes advanced features like EDOF, FLC, AMR, and EDR, offering versatility for accomplishing a wide variety of tasks. AF7915MZT is compatible with the WF-20 Wi-Fi streamer.

Note: EDOF, EDR, and DPQ are available on Windows PC only.



USB 2.0



Adjustable
~10-220x



5 megapixel
2592 x 1944



With the Extended Dynamic Range (EDR) feature, the details of darker or brighter areas within the object can be revealed by stacking images at different exposure levels. The Extended Depth of Field (EDOF) feature automatically stacks images at different focus level to improve the depth of field on rough or uneven surfaces. With the built-in Automatic Magnification Reading (AMR), measurements can be performed easily and quickly. Because of the built-in polarization filter this model is ideal when working with shiny or reflective objects such as metal, plastic, glass, jewelry, electronics, etc.

The main features of the AF7915MZT are:

- 5 Megapixel Edge sensor
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- Automatic Magnification Reading (AMR)
- Adjustable polarizer
- Flexible LED Control (FLC)
- Wireless Ready
- And more...

(*EDOF/EDR only functions under Windows OS)

Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	142.6	39.6	29.7	26.0
20	60.1	19.8	14.8	7.0
30	33.6	13.2	9.9	3.3
40	21.0	9.9	7.4	2.0
50	14.0	7.9	5.9	1.4

60	9.8	6.6	4.9	1.0
70	7.3	5.7	4.2	0.8
80	5.7	4.9	3.7	0.6
90	4.8	4.4	3.3	0.5
100	4.3	4.0	3.0	0.4
110	4.2	3.6	2.7	0.4
120	4.3	3.3	2.5	0.3
130	4.7	3.0	2.3	0.3
140	5.2	2.8	2.1	0.3
150	5.8	2.6	2.0	0.3
160	6.5	2.5	1.9	0.2
170	7.3	2.3	1.8	0.2
180	8.1	2.2	1.6	0.2
190	9.1	2.1	1.6	0.2
200	10.0	2.0	1.5	0.2
210	11.0	1.9	1.4	0.2
220	12.1	1.8	1.3	0.2
Listed values may differ slightly		* Without front cap		Unit = mm

Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	5.0 Megapixel (2592x1944)
Maximum frame rate	30 fps
Compatibility	

Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	PNG, JPEG
Supported video formats (MacOS)	MOV (max 1.3MP)
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-20 (optional)
Housing	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	11.5cm (L) x 3.4cm (D)
Weight	97g
Cable length	1.8m
Features	
Special feature	Automatic Magnification Reading (AMR), Extended Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC).
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	Yes
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€1100,00 - €1300,00