

AM4113T-FVW

Marka:
Ürün Kodu: AM4113T-FVW



Short Description

1.3 Megapixel resolution
395 nm + white LEDs
10-70x & 200xm magnification

Açıklama

The VW series has two types of LED lights that are switchable between white and UV light. This model has a filter to filter out the returning UV light so that an image with natural colors can be obtained.



USB 2.0



Measurement
functionality



Adjustable
~10-70x & 200x



Magnification
lock



1.3 megapixel
1280 x 1024



UV-LEDs
395nm



Switchable
UV/white LEDs



Standard working
distance

» Also available in a version with ~375nm LEDs (model AM4113T-FV2W)


Working distance/field of view/depth of field

MAGNIFICATION RATE WORKING DISTANCE FIELD OF VIEW(X) FIELD OF VIEW(Y) DEPTH OF FIELD
Unit = mm

Listed values may differ slightly

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
20	48.7	19.6	15.6	3.6
30	21.7	13.0	10.4	1.9
40	9.0	9.8	7.8	-
50	1.9	7.8	6.3	0.88
60	-2.3	6.5	5.2	-
220	-0.1	1.8	1.4	0.20
230	1.0	1.7	1.4	-
240	2.1	1.6	1.3	-

Special Light



Özellikler

Lighting	
Light/ LED type	395 nm UV + white
Number of LEDs	4+4
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	No
Emission filter	Yes, Emission barrier filter 400 nm
Polarizer	No
Optics	
Magnification	10x ~ 70x, 200x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	

Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXscope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV
Imaging standards	DirectShow, UVC
Wifi	Wireless-ready, requires the WF-10 WiFi streamer (optional)
Housing	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	105g
Cable length	1.8m
Features	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€400,00 - €600,00

Product Gallery

