

# AM4115T-FUW - EDGE

**Marka:**

**Ürün Kodu:** AM4115T-FUW - EDGE



## Short Description

1.3 Megapixel resolution

Versatility due to exchangeable caps

~375nm + white LEDs

20-220x magnification

## Açıklama

The UW series has two types of LED lights that are switchable between white and UV light. This model has a filter to filter out the returning UV light so that an image with natural colors can be obtained.



USB 2.0



Measurement  
functionality



Adjustable  
~20x-220x



Magnification  
lock




1.3 megapixel  
1280 x 1024



UV-LEDs  
375 nm



Switchable  
UV/white LEDs



Exchangeable  
cap



Long working  
distance


The Dino-Lite Edge models provide superior image quality and a high level of flexibility due to the adaptable cap design.

» Also available with 390-400nm LEDs (model AM4115T-FVW).

**Working distance/field of view/depth of field**

MAGNIFICATION RATE	WORKING DISTANCE	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
Listed values may differ slightly	* Without front cap			Unit = mm
20	60.2	19.5	15.6	2.5
30	33.5	13.0	10.4	1.8
40	20.9	9.8	7.8	1.5
50	13.9	7.8	6.3	-
60	9.7	6.5	5.2	-
70	7.1	5.6	4.5	1.0
80	5.5	4.9	3.9	-
90	4.5	4.3	3.5	-
100	4.1	3.9	3.1	-
110	4.0	3.6	2.8	-
120	4.1	3.3	2.6	-
130	4.5	3.0	2.4	-
140	5.0	2.8	2.2	-
150	5.6	2.6	2.1	-
160	6.3	2.4	2.0	-
170	7.1	2.3	1.8	-
180	8.0	2.2	1.7	-
190	8.9	2.1	1.6	-
200	9.9	2.0	1.6	-
210	10.9	1.9	1.5	-
220	11.9	1.8	1.4	0.1

**Special Light**



## Özellikler

Lighting	
Light/ LED type	~375 nm UV + white
Number of LEDs	4+4
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	Yes, Emission barrier filter 375 nm
Polarizer	No
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.9 and up
Software	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats (MacOS)	MOV

Imaging standards	DirectShow, UVC
Housing	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	100g
Cable length	1.8m
Features	
Special feature	No
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
Information	
Package contents	Microscope, carry pouch, software CD, calibration target, user manual, Microscope, carry pouch, software CD, calibration target, user manual, N3C-C (Close Cap) N3C-EB (Extended Open Black Cap) N3C-L (Long Cap) N3C-OB (Black Open Cap) N3C-S (Sidelight Cap)
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€600,00 - €800,00