

# AM5218MZT Edge

**Marka:**

**Ürün Kodu:** AM5218MZT Edge



## Short Description

Direct DVI connection

Robust metal housing

10-70, 200x magnification

Polarizer (anti-reflection)

High 720p HD resolution

## Açıklama

The Dino-Lite AM5218MZT Edge can be connected directly to a HDTV or a LCD monitor through a direct digital DVI/HDMI interface. It offers sharp and vibrant HD 720p resolution to display even the smallest details.



DVI  
connector



High speed



Adjustable  
~20x-220x



Exchangeable  
cap



HD  
720 p



8 White LEDs  
switchable



Metal  
housing



Standard working  
distance



Polarizer  
anti-reflection



Magnification  
lock

The AM5218MZT Edge is the ideal choice in situations, where real time images are vital, such as working on PCB's or other miniature objects. By tapping the Microtouch sensor on the microscope, the image can be frozen for inspection of important details and by pressing the Microtouch sensor for 2 seconds the LEDs can be switched on and off. The aluminium housing offers enhanced protection and durability and has the best look and feel. The built-in adjustable polarizer reduces glare and reflection on shiny objects, such as metal surfaces, electronics, plastics etc.

**Working distance/field of view/depth of field**

<b>MAGNIFICATION RATE</b>	<b>WORKING DISTANCE</b>	<b>FIELD OF VIEW(X)</b>	<b>FIELD OF VIEW(Y)</b>	<b>DEPTH OF FIELD</b>
<b>20</b>	60.2	19.5	11.7	2.5
<b>30</b>	33.5	13	7.8	1.8
<b>40</b>	20.9	9.8	5.9	1.5
<b>50</b>	13.9	7.8	4.7	
<b>60</b>	9.7	6.5	3.9	
<b>70</b>	7.1	5.6	3.4	1
<b>80</b>	5.5	4.9	3	
<b>90</b>	4.5	4.3	2.6	
<b>100</b>	4.1	3.9	2.3	
<b>110</b>	4	3.6	2.1	
<b>120</b>	4.1	3.3	2	
<b>130</b>	4.5	3	1.8	
<b>140</b>	5	2.8	1.7	
<b>150</b>	5.6	2.6	1.6	
<b>160</b>	6.3	2.4	1.5	
<b>170</b>	7.1	2.3	1.4	
<b>180</b>	8	2.2	1.3	
<b>190</b>	8.9	2.1	1.2	
<b>200</b>	9.9	2	1.2	
<b>210</b>	10.9	1.9	1.1	
<b>220</b>	11.9	1.8	1.1	0.1

Listed values  
may differ  
slightly

**Unit = mm**

## Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	20x ~ 220x
Macro zoom	No
Working distance	Standard
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	HD 720p
Maximum frame rate	60 fps
Compatibility	
Interface	DVI & HDMI
Wifi	No
Housing	
Housing material	Metal housing
Magnification lock	Yes
Dimensions	10.5cm (L) x 3.2cm (D)
Weight	125g
Cable length	1.8m
Features	
Special feature	No
Measurement	No
Calibration	No
Microtouch sensor	Yes
ESD safe	Yes
Information	
Package contents	Microscope, carry pouch, DVI & HDMI cable, power adapter, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- Diffuser cap, N3C-E- Extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS
Price range	€900,00 - €1100,00

**Product Gallery**