

AM7515MT1A



Marka:
Ürün Kodu: AM7515MT1A

Short Description


5 Megapixel resolution
70x ~ 140x magnification
Coaxial and brightfield illumination
Flexible LED Control (FLC)
Automatic Magnification Reading (AMR)

Açıklama

The AM7515MT1A is a 5MP Dino-Lite Edge Series microscope that has a magnification range of 70x ~ 140x with built-in coaxial illumination. By using the Flexible LED Control (FLC), this model is capable of switching between or mixing, brightfield and coaxial illumination.



USB 2.0



Measurement
functionality



Adjustable
~70x-140x




Standard working
distance



Flexible LED
Control FLC



Automatic
Magnification
Reading (AMR)



The coaxial illumination technique reveals details that are very difficult to see under normal light. The AM7515MT1A includes the Automatic Magnification Reading (AMR) feature which automatically detects and displays the magnification in the included Dino-Lite software. These unique features make the Dino-Lite AM7515MT1A a great inspection tool for material analysis, electronics inspection, or any similar application that requires, coaxial illumination, versatility and mobility. The Dino-Lite AM7515MT1A is bundled with the user-friendly DinoCapture 2.0 software for Windows.

For this model it includes functions such as:

- Automatic Magnification Reading (AMR)
- Flexible LED Control (FLC)
- Calibration
- Measurement
- Capturing & annotating images
- And recording video

Working distance/field of view/depth of field

| MAGNIFICATION RATE | WORKING DISTANCE* | FIELD OF VIEW(X) | FIELD OF VIEW(Y) | DEPTH OF FIELD |
|---------------------------|--------------------------|-------------------------|-------------------------|-----------------------|
| 70 | 38.6 | 5.6 | 4.2 | 0.77 |
| 80 | 36.2 | 4.9 | 3.7 | 0.62 |
| 90 | 34.8 | 4.3 | 3.3 | 0.52 |
| 100 | 34.2 | 3.9 | 2.9 | 0.44 |
| 110 | 34.0 | 3.6 | 2.7 | 0.38 |

| | | | | |
|--|---------------------------|-----|-----|------------------|
| 120 | 34.2 | 3.3 | 2.4 | 0.33 |
| 130 | 34.7 | 3.0 | 2.3 | 0.30 |
| 140 | 35.4 | 2.0 | 2.1 | 0.27 |
| Listed values may differ slightly | *Without front cap | | | Unit = mm |

Özellikler

| Lighting | |
|-----------------------------------|---|
| Light/ LED type | White |
| Number of LEDs | 8 |
| LED on/off switchable: | Yes |
| Infrared filter | IR cut-filter >650 nm |
| Diffuser available | Yes, N3C-D |
| Emission filter | No |
| Polarizer | No |
| Optics | |
| Magnification | 70x ~ 140x |
| Macro zoom | No |
| Working distance | Standard |
| Lens type | Glass with anti-reflection coating |
| Sensor | |
| Sensor type | CMOS |
| Resolution | 5.0 Megapixel (2592x1944) |
| Maximum frame rate | 30fps (max 20fps video recording) |
| Compatibility | |
| Interface | USB 2.0 |
| Operating system | Windows 7, 8, 10 & 11, MacOS 10.11.16 and up |
| Software | DinoCapture 2.0 (Windows), DinoXcope (Mac OS) |
| Supported image formats (Windows) | BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX |
| Supported video formats (Windows) | WMV, FLV, SWF |
| Supported image formats (MacOS) | JPEG, PNG |
| Supported video formats (MacOS) | MOV (max 1.3MP) |
| Imaging standards | DirectShow, UVC |

| | |
|----------------------|---|
| Wifi | Wireless-ready, requires the WF-10 WiFi streamer (optional) |
| Housing | |
| Housing material | Metal housing |
| Magnification lock | Yes |
| Dimensions | 10.7cm (L) x 3.2cm (D) |
| Weight | 139g |
| Cable length | 1.8m |
| Features | |
| Special feature | Automatic Magnification Reading (AMR), Flexible LED Control (FLC), Coaxial illumination |
| Measurement | Yes |
| Calibration | Yes |
| Microtouch sensor | Yes |
| ESD safe | Yes |
| Information | |
| Package contents | Microscope, carry pouch, software CD, user manual, quick guide, calibration target, front cover box |
| Warranty information | 2 years European warranty |
| Regulatory approval | CE, FCC, ROHS |
| Price range | €1000,00 - €1200,00 |

Product Gallery