

# AM8517MZTL



**Marka:**

**Ürün Kodu:** AM8517MZTL Edge Plus

## Short Description

High Optical Resolution

8.0 Megapixel

Enhanced Flexible LED Control (eFLC)

Automatic Magnification Reading (AMR)

Long Working Distance

## Açıklama

Capture stunning images with the AM8517MZTL 8-megapixel long working distance digital microscope. Engineered with a comprehensive set of features, including AMR, this model is designed to excel in both imaging and measurement-oriented tasks.



Metal  
housing



Enhanced Flexible  
LED control



Adjustable  
~10x - 140x




8,0 Megapixels  
3840 x 2160



Measurement  
functionality



8 White LEDs  
switchable



Polarizer  
anti-reflection



Automatic  
Magnification  
Reading (AMR)



Long working  
distance

**The main features of the AM8517MZTL are:**

- 8 Megapixels
- High Optical Resolution
- Automatic Magnification Reading (AMR)
- Enhanced Flexible LED Control (eFLC)
- Long Working Distance (LWD) Optics
- Adjustable Polarizer
- Robust Metal Housing
- 10x ~ 140x magnification (Edge shading occurs below 25x when previewing in 16:9 windows.)
- And more...

### Optical Data Table

MAGNIFICATION RATE	WORKING DISTANCE *	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
10	238.3	60.69	34.14	25.99
20	115.4	30.35	17.07	6.94
30	75.9	20.23	11.38	3.29
40	57.1	15.17	8.53	2.00
50	46.7	12.14	6.83	1.42
60	40.5	10.11	5.69	1.09
70	36.7	8.67	4.88	0.87
80	34.3	7.59	4.27	0.72
90	32.9	6.74	3.79	0.62
100	32.3	6.07	3.41	0.53
110	32.1	5.52	3.10	0.47
120	32.3	5.06	2.85	0.42
130	32.8	4.67	2.63	0.38
140	33.5	4.34	2.44	0.35

Listed values may differ slightly \* Without front cap

Unit = mm

### Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
Optics	
Magnification	10x ~ 140x
Working distance	238.3 ~ 33.5 mm
Sensor	
Sensor type	CMOS
Resolution	8.0 Megapixel (3840x2160)

Maximum frame rate	10 fps at 8.0 MP, MJPEG 25 fps at 2.0 MP, MJPEG
<b>Compatibility</b>	
Interface	USB 2.0
Operating system	Windows 10/11
Supported image formats (Windows)	BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM
Supported video formats (Windows)	WMV, FLV, SWF
<b>Housing</b>	
Housing material	Metal housing
Dimensions	130 mm (H) x 33 mm (D)
Weight	120 g
<b>Features</b>	
Special feature	Auto and Manual Refocus
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
<b>Information</b>	
Package contents	N3C-C (Close Cap) N3C-D (Diffuser Cap) N3C-D2 (Opal Diffuser Cap) N3C-E (Extended Open Cap) N3C-L (Long Cap) N3C-O (Open Cap) N3C-S (Sidelight Cap)
Warranty information	2 years European warranty
Regulatory approval:	CE, FCC, ROHS
Price range	€1200,00 - €1400,00