

# WF4915ZTL



**Marka:**

**Ürün Kodu:** WF4915ZTL - Wireless

## Short Description

1.3 Megapixel Edge sensor  
Extended Depth of Field (EDOF)  
Extended Dynamic Range (EDR)  
Flexible LED Control (FLC)  
Automatic Magnification Reading (AMR)

## Açıklama

The Dino-Lite WF4915ZTL is a Wireless model that is part of the Long Working Distance (LWD) series. Go from wireless to wired and back in an instant. Work wired via USB or work wireless with the attachable WF-20 Wireless adapter.



USB 2.0



1,3 Megapixels  
1280 x 1024



Adjustable  
~10x - 140x



Magnification  
lock



Polarizer  
anti-reflection



Long working  
distance



Flexible LED  
Control FLC



Exchangeable  
cap



Automatic  
Magnification  
Reading (AMR)



The WF4915ZTL is equipped with premium features such as Extended Depth of Field (EDOF), Extended Dynamic Range (EDR), Flexible LED Control (FLC), integrated polarizer, extensive measurement functionality and Automatic Magnification Reading (AMR) for measurement-intensive applications.

**The main features of the WF4915ZTL are:**

- Completely wireless solution (including WF20)
- 10-140x magnification
- 1.3 Megapixel Edge sensor
- Extended Depth of Field (EDOF)
- Extended Dynamic Range (EDR)
- Automatic Magnification Reading (AMR)
- Adjustable polarizer
- Flexible LED Control (FLC)
- And more...

*(\*EDOF/EDR only functions under Windows OS)*

**Working distance/field of view/depth of field**

Magnification Rate	Working Distance *	Field of View(x)	Field of View(y)	Depth of Field
<b>Listed values may differ slightly</b>	<b>* Without front cap</b>			<b>Unit = mm</b>
10	234.5	39.0	31.2	12
20	112.5	19.5	15.6	4.5
30	72.5	13.0	10.4	3.1
40	54.5	9.8	7.8	1.8
50	43.5	7.8	6.2	1.2
60	37.5	6.5	5.2	0.9
70	33.7	5.6	4.5	0.6

80	31.3	4.9	3.9	0.5
90	29.9	4.3	3.5	0.37
100	29.2	3.9	3.1	0.28
110	29.1	3.5	2.8	0.22
120	29.3	3.3	2.6	0.17
130	29.8	3.0	2.4	0.12
140	30.5	2.8	2.2	0.09

## Özellikler

Lighting	
Light/ LED type	White
Number of LEDs	8
LED on/off switchable:	Yes
Infrared filter	IR cut-filter >650 nm
Diffuser available	Yes (N3C-D included)
Emission filter	No
Polarizer	Yes, linear
Optics	
Magnification	10x ~ 140x
Macro zoom	No
Working distance	Long
Lens type	Glass with anti-reflection coating
Sensor	
Sensor type	CMOS
Resolution	1.3 Megapixel (1280x1024)
Maximum frame rate	30 fps
Compatibility	
Interface	USB 2.0
Operating system	Windows 7, 8, 10 & 11, MacOS 10.11.6 and up (cable only)
Software	DinoCapture 2.0 (Windows) cable + wireless, DinoXcope (Mac OS) cable only, DinoConnect wireless only
Supported image formats (Windows)	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows)	WMV, FLV, SWF
Supported image formats (MacOS)	JPEG, PNG
Supported video formats	MOV

(MacOS)	
Imaging standards	DirectShow, UVC
Wifi	Yes
<b>Housing</b>	
Housing material	Composite/ plastic housing
Magnification lock	Yes
Dimensions	11.4cm (L) x 3.3cm (D)
Weight	111g
Cable length	1.8m
<b>Features</b>	
Special feature	Automatic Magnification Reading (AMR), Extended Dynamic Range (EDR), Extended Depth of Field (EDOF), Flexible LED Control (FLC)
Measurement	Yes
Calibration	Yes
Microtouch sensor	Yes
ESD safe	No
<b>Information</b>	
Package contents	Microscope, WF-20, carry pouch, software CD, calibration target, user manual, N3C-O- Open cap, N3C-C- Closed cap, N3C-D- diffuser cap, N3C-E- extension cap, N3C-L- Long cap, N3C-S- Side light cap
Warranty information	2 years European warranty
Regulatory approval	CE, FCC, ROHS, UKCA – available upon request – <a href="mailto:marketing@dino-lite.eu">marketing@dino-lite.eu</a>
Price range	€1100,00 - €1300,00

## Product Gallery

